

C532dn Specifications

OKI®

FINALLY, AN HD COLOR PRINTER THAT'S PREPARED TO GROW WITH YOUR BUSINESS

The fast and reliable C532dn color printer, with OKI LED technology and a powerful new engine, is built to support small workgroups and businesses that require expanded performance with excellent HD color output and security.

Key Features

- HD Color LED printing technology with multi-level output quality
- Fast, New Engine
- Flexible media capabilities including up to 52" banners and a variety of heavy stock media
- Paper capacity up to 1,410 sheets with two optional trays
- Security features protecting your documents, your devices and your network
- Google Cloud Print 2.0 ready enabling printing on the move and direct printing using Local Mode



Simplicity

- Easy to set-up and get started
- As new features become available, update the device via the OKI portal
- Quiet mode is ideal for smaller offices



Security Features

- Internet Protocol Security (IPSec) compliance, ensuring that documents are safely sent and received
- Keep documents confidential with Private Print and optional Card Release while selecting which jobs to print



Advanced Connectivity

- Wireless Direct offers safe simultaneous connection of wired and wireless networking
- Gigabit Ethernet enables fast transfer of large color files across the network
- Google Cloud Print 2.0 and Apple AirPrint® ready, enabling printing on the move
- Optional Wireless LAN Module available



Cost and energy saving

- Print marketing materials in-house with outstanding print quality and media flexibility
- Deep Sleep mode saves energy, Auto-Off mode automatically powers down to less than 0.5W when not in use
- Toner Save to reduce cost, when printing draft or internal documents
- Standard duplex printing to reduce paper usage
- Robust and long-lasting OKI LED technology

Letter / A4	✓
Color / Mono	✓
Networked / Duplex	✓
1 – 20 users / Small Workgroup	✓

C532dn COLOR PRINTER

Printer		Environmental	
Print speed	Up to 31ppm Color/Mono ¹	Size (WxDxH)	16.8" x 22.5" x 11" (427mm x 571mm x 279mm)
Time to First Page	7.5 seconds Color/Mono ¹	Weight	Approx. 50.7 lbs (23.0 kg)
Processor	ARM Processor 667 MHz	Acoustic Noise	Operating 54dBA; Standby 37dBA; Power Save Inaudible
Print Resolution	up to 1200 x 1200 dpi	Power Consumption	Typical: 670W; Max: 1220W; Idle: 90W; Power Save: <14W; Deep Sleep: <1.1W; Auto-Off: <0.5W
Monthly Duty Cycle	Maximum 60,000 pgs/month Recommended up to 6,000 pgs/month		
Operator Panel	2.4" Mono Graphic Display		
Memory	1GB RAM; 3GB eMMC (Program + font area: 0.25GB, Data Storage Area: 2.75GB)		
Interface and Software		Warranty	
Connectivity	USB 2.0 Device, 10Base-T/100Base-TX/1000Base-T Ethernet, Host USB x 2 (front); Wireless (Option) IEEE802.11a/b/g/n	Printer	1-Year On Site ²
Printer Languages	PCL6 (XL3.0) and PCL5c, Postscript 3 (emulation), IBM-PPR, EPSON-FX, XPS, PDF (V1.7)	LED Printheads	5-Year limited warranty
Network Protocols	TCP/IPv4&v6, NetBIOS over TCP, DHCP, DHCPv6, BOOTP, HTTP, HTTPS, DNS, DDNS, WINS, UPNP, Bonjour, SMTP, SMTPS, POP3, SNMPv1&v3, SNTP, IPP, IPPS, WSD Print, LLTD, IEEE802.1X, LPR, Port9100, Telnet, FTP, FTPS, IPsec, AirPrint, Google Cloud Print 2.0, Wireless IEEE802.11a/b/g/n, WEP, WPA(Personal, Enterprise), WPA2(Personal, Enterprise)		
Operating Systems	Vista (32-bit & 64-bit) / Server 2008 (32-bit & 64-bit) / Windows 7 (32-bit & 64-bit) / Server 2008 R2 (64-bit) / Windows 8 (32-bit & 64-bit) / Server 2012 (64-bit) / Windows 8.1 (32-bit & 64-bit) / Server 2012 R2 (64-bit) / Windows 10 (32-bit & 64-bit); Linux PPD; Mac OS X 10.8.5 to 10.11		
Utility Suite	Configuration Tool ⁵ , Color Correct Utility, Color Swatch Utility ⁵ , Driver Installer ⁵ , Firmware Update Tool, Front End Installer ⁵ , LPR Utility ⁵ , Network Card Setup ⁵ , Network Extension ⁵ , PDF Print Direct ⁵ , Print Job Accounting Client, PS Gamma Adjuster, Profile Assistant ⁶ , smart PrintSuperVision ⁵ , Web Driver Installer ⁵		
Typefaces		OKIcare® WARRANTY ENHANCEMENT PROGRAMS (ORDER NUMBERS)	
Printer Fonts	Scalable: 87 PCL fonts, 80 PostScript fonts	2-Year Depot	38042812
Bitmap Fonts	4 PCL fonts (Line Printer, OCR-A/B, USPS ZIP Barcode)	3-Year Depot	38042813
Barcode	10 types of one dimension with 26 variations: UPC-A, UPC-E, EAN/JAN-8, EAN/JAN-13, Interleaved2of5, Code39, Code 128, EAN/UCC-128, CODABAR, ZIP+4POSTNET; 2 types of two dimensions: PDF417, QR code	4-Year Depot	38042814
Paper Handling		5-Year Depot	38042815
Input Capacity	350 sheets of 80gsm Standard (250-sheet Main Tray + 100-sheet Multi-Purpose Tray); 1,410 sheets Max (with Optional 530-sheet 2nd & 3rd Trays)	2-Year On-Site	38042912
Paper Sizes	Main Tray from 3.9"x 5.8" to 8.5" x 14"; Multi-Purpose Tray from 2.5" x 3.5" to 8.5" x 52" banners; Duplex/Optional Trays from 5.8" x 8.3" to 8.5" x 14"	3-Year On-Site	38042913
Paper Weight	Main Tray / Duplex / Option Trays 16-47lb Bond (64-176gsm); Multi-Purpose Tray 16-58lb Bond (64-220gsm)	4-Year On-Site	38042914
Paper Output Capacity	Main Output Bin 150 sheets face down	5-Year On-Site	38042915
Duplex (2-sided) Printing	Standard		
		Note: All Warranty Enhancement Program options extend the total warranty coverage period from the date of purchase to the number of years listed for each order number above.	
H/W		Consumables (Order Numbers)	
		Toner cartridges ³ (3,000 pages)	Cyan: 46490503; Magenta: 46490502; Yellow: 46490501
		Toner cartridges ³ (3,500 pages)	Black: 46490504
		High capacity toner cartridges ³ (6,000 pages)	Cyan: 46490603; Magenta: 46490602; Yellow: 46490601
		High capacity toner cartridge ³ (7,000 pages)	Black: 46490604
		Image drums ⁴ (30,000 pages)	Cyan: 46484103; Magenta: 46484102; Yellow: 46484101; Black: 46484104
Options (Order Numbers)			
		530-sheet 2nd/3rd Paper Tray	46361801
		Cabinet w/ Casters	46567702
		IEEE802.11a/b/g/n Wireless	45830201

¹ Published performance results based on laboratory testing. Individual results may apply.

² Available in the U.S. and Canada only.

³ Average A4 continuous print page yield in accordance with ISO/IEC 19798. Individual results may vary. Printer shipped with toner for 2,000 A4 pages.

⁴ Estimated average life, based on 3 pages per job.

⁵ Windows only.

⁶ Mac OSX only.

Specifications are subject to change without notice.

Google
Cloud Print 2.0 Ready



Works with
Apple AirPrint

Oki Data Americas, Inc.

USA
8505 Freeport Pkwy., Suite 600
Irving, TX 75063
Tel: 800.OKI.DATA (800.654.3282)
Fax: 856.222.5320

www.oki.com/us

Canada
5800 Hurontario St., Suite 1020
Mississauga, Ontario L5R 4B9
Tel: 905.755.5800
Fax: 905.755.5840

www.oki.com/ca

© 2020 Oki Data Americas, Inc. Oki Reg. T.M., M.D., Oki Electric Industry Co., Ltd. Adobe Reg. T.M., PostScript 3 T.M., Adobe Systems, Inc. PCL Reg. T.M., Hewlett-Packard Co. Windows, Windows Vista Reg. T.M., Microsoft Corp. XPS Reg. T.M., Dell, Inc. Mac Reg T.M., Apple Inc. Harlequin Reg. T.M., MultiRIP, DirectPrint, T.M., Global Graphics Software Ltd. EFI Reg. T.M., Electronics for Imaging, Inc. AirPrint and the AirPrint logo are trademarks of Apple Inc. Google Cloud Print is a trademark of Google Inc.

MS16183-0420

OKI®