

Cutting Edge Thin & Zero Clients

V1206-PD Zero Client for VMware and Amazon WorkSpaces TFRA2 PCoIP® Portal Processor

Industry Leading VDI Performance

The 10ZiG V1206-PD is part of our V1200 Tera2 PCoIP® Zero Client Series optimized for VMware and Amazon WorkSpaces environments. With no operating system and no local storage, the V1200 Series line provides an ultra-secure yet powerful and easy to manage endpoint that eliminates the chance of viruses and provides extensive USB security and authentication features. With options ranging from dual through quad screen, PoE, Fiber, DVI-I, DVI-D, 4 DisplayPort and Internal Smart Card (CAC) with up to 6 USB 2.0 ports as well as standard TAA Compliance on all V1200 Series Zero Clients, you can be confident in finding a device that will fit your ideal use case environment.

The V1206-PD model highlighted below supports dual screens and comes equipped with 1 x DisplayPort and 1 x DVI-I and 6 x USB 2.0 along with a Fiber option. All 10ZiG V1200 Series PCoIP® Zero Clients receive a one-year, free subscription to the Teradici Desktop Access Plan. The Desktop Access Plan includes the Teradici Management Console with a subscription to firmware and security updates as well as tech support.



► TERA2 PCoIP Portal Processor, Tera 2321 PCoIP Chipset
 ► 1 x DisplayPort + 1 x DVI-I
 ► 6 x USB 2.0
 ► Optional Fiber
 ► Optional VESA Mount
 ► TAA Compliant
 ► 1 year free subscription to Teradici Desktop Access Plan

vmware

PCoIP

CİTRIX



Microsoft



V1206-PD Zero Client

10ZiG®

Tera2 PCoIP Zero Client Series



SPECIFICATIONS

- 1. Power Button/Power LED
- 2. USB 2.0 (4)
- 3. Line Out
- 4. Mic In
- **5.** USB 2.0 (2)
- **6.** RJ45 LAN
- **7.** DVI-I
- 8. DisplayPort
- 9. DC Jack
- 10. Kensington Lock

System Specifications	
Management Utility	Teradici Management
Form Factor	Slim Line
Processor	Teradici PCoIP® Portal Processor - TERA2
Chipset	TERA2321 PCoIP®
Dimensions	
Device	5.21" (D) x 1.06" (W) x 6.77" (H) - 132mm x 27mm x 172mm
Weight	2.53lbs (1.15kgs)
Connections	
Ports	6 x USB 2.0, 1 x Mic In, 2 x Line Out
Video/Resolution	1 Monitor at 2560 x 1600 or 2 Monitors at 1920 x 1200, 1 x DisplayPort + 1 x DVI-I
Networking	
Ethernet	10/100/1000 Base-T
Fiber	Optional SFP Fiber Connector (100/1000Mbps)
Environmental	
Operating Temp.	32-104F (10-40C) 10-90% non-condensing humidity
Power	8 Watts, DC-12V/3A External Power Adapter
Certifications	
CE, FCC, CAN ICES-3/NMB-3, VCCI, UL, TUV-GS, C-Tick, GOST, BSMI, RoHS	















P: +1 (866) 865-5250 P: +44 (0) 116 214 8650 P: +61 2 80027421

P: +49(0) 6724 934-45

E: info@10ZiG.com E: info@10ZiG.eu E: info@10ZiG.com.au E: vertrieb@10zig.de



