



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cat5e 350 MHz Snagless Molded (UTP) Ethernet Cable (RJ45 M/M) - Orange, 5 ft. (1.52 m)

MODEL NUMBER: N001-005-OR











Color-coded Cat5e cable connects high-speed network components like computers, servers, printers, copiers, routers and switches in a home or office Cat5/5e application. Ideal for high-density data centers.

Features

An Ideal Solution for High-Speed Cat5/5e Networking

- Connects high-speed network components, such as computers, servers, printers, copiers, routers and switches
- Designed for 1000Base-T, 10/100Base-T, 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type 3 applications
- Provides high-speed connections up to 350 MHz/1 Gbps
- Flawless signal delivery with minimal near-end crosstalk levels

Snagless RJ45 Male Connectors

- Molded snagless boots prevent locking tabs from damage during installation
- Connectors and cable color-coded orange for easy ID in crowded applications

Premium Construction Ensures Excellent Performance

- Manufactured from 26 AWG 4-pair stranded UTP
- Gold-plated copper contacts for accurate signal transfer
- Molded integral strain relief for long life
- Durable corrosion-resistant PVC jacket
- Meets most current industry standards, including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (Cat5e draft 11)

Highlights

- Premium cabling for Cat5/5e applications
- Rated for 350 MHz/1 Gbps communications
- Snagless RJ45 male connectors
- 26 AWG 4-pair stranded UTP with PVC jacket
- Color-coded orange for easy identification

System Requirements

 For 1000Base-T (1Gbps Ethernet), 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type3 applications.

Package Includes

N001-005-OR Cat5e 350 MHz
 Snagless Molded UTP Patch
 Cable (RJ45 M/M), Orange, 5 ft.



Specifications

OVERVIEW	
UPC Code	037332202611
Technology	Cat5/5e
PHYSICAL	
Color	Orange
Cable Shielding	UTP
Cable Jacket Material	PVC
Cable Jacket Rating	СМ
Number of Conductors	4 Pair
Conductor Material	Stranded Copper
Conductor Gauge	26 AWG
Cable Length (ft.)	5
Cable Length (m)	1.5
Cable Length (in.)	60
Cable Length (cm)	152.4
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 22.86
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.00
Shipping Weight (kg)	0.09
Shipping Weight (lbs.)	0.20
COMMUNICATIONS	
Bandwidth per TIA Standard	100 MHz
Maximum Bandwidth as Tested	350 MHz
Maximum Data Rate	1Gbps
Network Speed	1Gbps
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Connector Type	Molded; Snagless
Wiring Configuration	EIA/TIA 568B
FEATURES & SPECIFICATIONS	
Cable Style	Unshielded; Molded; Snagless



Tripp Lite1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234

SPECIAL FEATURES		
IP68 Rated	No	
Snagless Connector	Yes	
Antibacterial	No	
STANDARDS & COMPLIANCE		
Certifications	RoHS Compliant	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies