

Mini DisplayPort 1.2a to HDMI Active Adapter Cable (M/M) - 4K 60 Hz, HDCP 2.2, 10 ft.

MODEL NUMBER: **P586-010-HD-V2A**



HDCP 2.2-compliant cable connects the Mini DisplayPort (mDP) or Thunderbolt port on your PC, Mac or tablet to a 4K-enabled HDMI monitor, projector or television.

Description

The P586-010-HD-V2A Mini DisplayPort 1.2a to HDMI Active Adapter Cable (M/M) connects an mDP- or Thunderbolt-enabled PC, Mac or tablet (such as the Surface Pro series) to the HDMI port on a 4K monitor, projector or television. With an mDP male connector on one end and a gold-plated high-grip HDMI male connector on the other, this cable requires no separate power adapter. It lets you continue using an existing 4K HDMI display without the extra expense of buying a new mDP monitor.

Recommended for displaying crystal-clear video on a large monitor or digital sign, this cable supports UHD video resolutions up to 4K @ 60 Hz (3840 x 2160) as specified in HDMI 2.0. The P586-010-HD-V2A also supports rich, full audio (if your DisplayPort card supports audio passthrough) and the latest HDCP 2.2 (High-Bandwidth Digital Content Protection) standards.

Because it's an active adapter, the 10-foot (3.1-meter) P586-010-HD-V2A is compatible with Single-Mode and Dual-Mode (DP++) DisplayPort output. It's perfect for use with graphics cards, such as AMD Eyefinity, that don't output DP++ signals.

The corrosion-resistant gold-plated HDMI connector and contacts provide maximum conductivity and minimize data loss. Its special high-grip plug prevents a loose or accidentally disconnected cable from causing picture loss. Integral strain relief with ridges on each end gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking.

Features

Send UHD Mini DisplayPort 1.2a Signals to a 4K HDMI Display Connects mDP or Thunderbolt PC, Mac or tablet to a 4K-enabled HDMI monitor, projector or HDTV
Recommended for displaying video on a large monitor or digital sign mDP and high-grip HDMI male connectors
No separate power adapter required
Vibrant Video Quality Supports UHD video resolutions up to 4K @ 60 Hz (3840 x 2160) as specified in HDMI 2.0
Supports HDCP 2.2 audio and EDID Active adapter compatible with Single-Mode and Dual-Mode (DP++) DisplayPort output
Recommended for graphics cards, such as AMD Eyefinity, that don't output DP++ signals

Superior Materials for Superior Performance Gold-plated HDMI connector and contacts for maximum conductivity and minimum data loss
Special high-grip HDMI plug prevents accidental disconnections
Integral strain relief provides cable and connectors with flexibility and reduces stress

Highlights

- Supports video resolutions up to 4K @ 60 Hz (3840 x 2160)
- Compliant with latest HDCP 2.2 standards
- No separate power adapter required
- High-grip HDMI plug prevents accidental disconnections
- Supports EDID specifications

Package Includes

- P586-010-HD-V2A Mini DisplayPort 1.2a to HDMI Active Adapter Cable (M/M), 10 ft.



Specifications

OVERVIEW	
UPC Code	037332200617
Technology	HDMI; DisplayPort
VIDEO	
Max Supported Video Resolution	4K @ 60 Hz (3840 x 2160)
Max Supported Color Depth	8-bit
HDR Support	Yes
PHYSICAL	
Color	Black
Cable Outer Diameter (OD)	5.0 +/- 15mm
Cable Jacket Rating	VW-1
Wire Gauge (AWG)	32
Cable Length (ft.)	10
Cable Length (m)	3
Cable Length (in.)	120
Material of Construction	ABS, PVC
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.21
Shipping Weight (lbs.)	0.46
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 °F (0 to 40 °C)
Storage Temperature Range	-4 to 140 °F (-20 to 60 °C)
Operating Humidity Range	10 to 90%, Non-Condensing
Storage Humidity Range	10 to 90%, Non-Condensing
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (MALE)
Connector Plating	Gold; Nickel
Contact Plating	Gold



FEATURES & SPECIFICATIONS	
Displayport Specification	1.2a
HDCP Specification	2.2
STANDARDS & COMPLIANCE	
Certifications	CE, FCC, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty
Product Warranty Period (U.S. & Canada)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>