

GIGABYTE™

GB-BKi7HA-7500

6th gen Intel® Core™ processors

Mini PC of the New Generation



SPECIFICATION

CPU:	Intel® 7th generation Core™ i7-7500U 2.7GHz / 3.7GHz
MEMORY:	2 x SO-DIMM DDR4 slots
LAN:	Gigabit LAN (Intel i219LM)
EXPANSION:	1 x M.2 slot (2280_storage) PCIe /SATA 1 x PCIe M.2 NGFF 2230 A-E key slot occupied by the WiFi+BT card
AUDIO:	Realtek ALC255
GRAPHICS:	Intel® HD Graphics 620
FRONT I/O:	1 x USB 3.1 type C, 1 x USB3.1 1 x head phone jack with MIC
REAR I/O:	1 x HDMI (2.0), 1 x Mini DisplayPort (1.2) 2 x USB 3.0, 1 x RJ45, 1 x DC-In, 1 x Kensington lock slot
VESA:	Bracket included Supports 75 x 75 and 100 x 100 mm

DIMENSION: 46.8 mm x 112.6 mm x 119.4 mm (1.84" x 4.43" x 4.7")

UPC Code: 889523006948

Dimension(in): 21.69*17.16*8.38 inches

Gross Weight: 16.49 lbs

Quantity per Carton: 8



Size: 46.8 x 112.6 x 119.4mm



Wireless Module*

(IEEE 802.11 ac WIFI + Bluetooth 4.2)

* Wireless module inclusion may vary based on local distribution

4K

DISPLAY
Support



Hard Drive tray (Supports one 2.5" SATA 6Gbps HDD)
* Hard Drive is not included