





TECHNICAL SPECS

- 3000vA Rack Mount UPS with Pure Sine Wave Output with 8 Outlets
- Boost and Buck AVR automatically adjusts for under-voltage and overvoltage ensuring stable power and longer life batteries.
- ECO (Efficiency Corrective Optimizer) for energy saving and EPO function (Emergency Power Off)

EAN 662919095227

Outlets

Surge Protection 720 Joules

Noise Level Less than 45dB

Backup Runtime 11.8 minute half load, 3.7 minute full load

Recharge Time 4 hours recover to 90% capacity

Load Capacity (Watts) 2700VA

Transfer Time 4 ms (max 8ms)

Waveform Type Pure Sine Wave

DESCRIPTION

Go big with the 3000VA Rack Mount UPS from V7, our most powerful UPS. It provides backup power for mission critical equipment in server rooms, data centers, and other vital equipment. It ensures a consistent flow of electricity to help prevent costly equipment failure and data loss during power failures, brownouts, or other power issues. Featuring Auto Voltage Regulation (AVR) to adjust for under-voltage and over-voltage to ensure stable power, the Rack Mount UPS also features an Efficiency Corrective Optimizer (ECO) to maximize energy savings. Additionally, the Rack Mount UPS enables you to manage backup time to critical devices with programmable...