

# Chromebase Mini

*Smaller Surface. Superior Service.  
Commercial Grade Chromebase 10" All-in-One Multi-Touch Solution.*

Introducing the Chromebase Mini 10" Multi-touch solution, an ultra-thin and powerful device specifically designed for commercial and corporate usage with a high-touch experience.

The Chromebase Mini is a solid-state interactive solution designed to be extremely reliable and secure, making it ideal for interactive public displays in high traffic environments (i.e. digital signage, POS, kiosk, meeting room management or corporate environments).

Chrome Device Management allows administrators to manage their organization's Chrome devices from a central place. Integrators can also use the signage app of their preference available via the Chrome Web Store to control what's on the screen.

## *The advantages of the Chromebase Mini:*

- A commercial grade multi-touch, all-in-one solution.
- Tough and retail-hardened design for 24/7 operability in public spaces.
- High quality camera and speakers that meet Chrome video conference and Hangouts Requirements.
- Wide viewing angles in landscape and portrait.
- Multiple mounting options: recessed surfaces, wall mounts and kiosks.
- Optional Chrome Device Management to save valuable time, installation cost, programming and maintenance.






29.9 mm



Remove I/O Cover



Audio Combo Jack   HDMI Port   LAN Port   Power Input   USB2.0 with BC1.2

## Chromebase Mini 10"

Specifications		Front Panel	10.1" native resolution 1280x800 250nits Internal Stereo Digital MIC
Features	Enterprise Grade all-in-one multi-touch solution with Chrome OS. Operating temp <40°C/104°F, shockproof, fanless, and solid state, dust and water resistant front panel, for commercial environments, APAR ( AC Power Auto Recovery)	Warranty	The Chromebase Mini comes with a 1 year warranty. Extended warranty optional for 3 years
Operating System	Chrome OS	USB 2.0 port	support BC1.2 x 3
CPU	Rockchip RK3288C Quad-Core Cortex-A17 turbo up to 1.8GHz	HDMI output	x 1
Graphics	ARM Mali-T764 MP4 GPU @ 600 MHz	RJ45 LAN	x 1 10/100/1000 Mb
Memory	Dual Channel 4GB, LPDDR3	Audio Combo Jack	x 1 (Mic/ earphone)
Chassis	IPX2 Compliant incl. cable cover SECC material - fanless design	Power switch	x 1 (Hidden Type)
Panel & Touch Panel	AHVA Panel 10.1" (1280x800) 250 Nits Support 10 points (PCT Multi Touch) IP54 dust and water protection	DC in 12~60V	power inlet Jack x 1
LAN	Gigabit Ethernet [RJ45]	Video I/O	FHD Webcam (2MP )
Audio	Maxim MX98090 Build in stereo digital mic. and speaker	Accessories	User Manual, Warranty and Support Card, Power Cord, Cable Cover (Knock-out Design), On/off pin tool Bundled desktop stand for landscape and portrait mode, cable clamp tie
Storage	EMMC 5.0 - 16 GB	Optional Accessories	VESA wall mount Various bases and mounts
Form Factor	Dimensions (WxHxD)	270 x 179 x 29.9 mm 10.63 x 7.05 x 1.18 inch	VESA
	Weight	1.22 kg / 2.69 lbs	Operating Temperature
	Color	Gun-metal black	Non-Operation Temperature
Networking	Giga LAN Realtek RTL8211E-VB with LED Wi-Fi+ Bluetooth; Wireless 802.11 b/g/n/ac+BT4.0 built-in 2.4/5Ghz Embedded Antenna		Relative Humidity
			Environment
		Operating Temperature	
		Non-Operation Temperature	
		Relative Humidity	
		IP54 (front) fanless design, IPX2(rear) compliance	

For more information on Chrome Mini products, visit us at [www.aopen.com/us](http://www.aopen.com/us).