

Aura Professional UC™ Conference Phone

Desktop PTSN, Softphone via USB and Cell via 3.5mm jack



You don't just need a new conferencing phone, you need one that does everything you need to do...

This Conferencing Phone Has All You Need

You need one that does everything. Connect it to your landline for standard conferencing. Connect to a PC/Mac via USB for VoIP functionality. Connect to your phone or tablet via the 3.5mm jack. You can even add in external mics, a power amplifier, or mixing console via the auxiliary audio ports.

Choose the Aura Professional UC™

- PSTN direct dial, redial, rapid dial, recall, second flash
- Make Skype conference calls using your PC/Mac
- Use the headset jack in your iOS or Android phone or tablet and even your cell phone can become a robust conference phone
- Call mute, call hold, three-way calling in all modes




Part	CP-3012
UPC	800807300484
MSRP	\$399.99

Aura Professional UC™ Conference Phone

Desktop PTSN, Softphone via USB and Cell via 3.5mm jack



❶ Microphone Mute	❶ Caller ID
❷ Call Hold	❷ Ring volume adjust
❸ Redial and Flash buttons	❸ Menu
❹ Volume up/down switches	❹ OK (Accept) button
❺ Standard keypad	❺ Green and Red microphone



Package Includes

- ❶ Conference Phone
- ❷ Audio Transfer Adapter
- ❸ USB Cable
- ❹ AC adapter f
- ❺ RJ-11 Cable
- ❻ Line In/Line Out Cable
- ❼ Power Extension Cable
- ❽ Junction Box
- ❾ Users Guide (not shown)

Optional

- External Microphone
- Microphone Cable



Specifications

FEATURES

- Wide-band acoustic echo cancellation with HD voice, dynamic noise suppression, automatic gain control, voice band equalization and intelligent microphone mixing.
- Four Internal uni-directional microphones.
- USB VoIP, suitable for PC/Mac, Video systems, UC communications.
- 3.5mm Jack for iOS and Android phone/tablet calls.
- Built in 4-way conferencing.
- Switch from analog phone calls, to USB VoIP calls, and to cell calls seamlessly.
- Auxillary port allows external devices to connect.
- Speaker volume up to 90dB.

AUDIO SPECIFICATIONS

DSP based deep echo cancellation: -65dB

Echo Tail: 500ms

Bi-directional Noise Suppression: -18dB

LEC : - 25 dB, length 32ms

USB VoIP or LINE IN/LINE OUT

ELECTRICAL SPECIFICATIONS

USB Connector: Standard B type

LINE IN/LINE OUT Connector: 3.5mm jack

Voice frequency response: 100Hz - 16kHz

TELEPHONE SPECIFICATIONS

Telephone Connection: Analog PBX or standard analog PSTN line

Telephone Connector: Standard RJ-11

Audio Frequency Band: 200Hz - 3400Hz

Certifications: FCC part 15 Class A, A-Tick, Canadian, UL, VCCI, RoHS

MECHANICAL SPECIFICATIONS

Dimensions Phone: 13.3" L x 2.5" H (33.8 x 6.3)cm


Weight: 1lb 10oz (740g)

Package: 14" x 14" x 4" (35.5 x 35.5 x 10.2)cm

Package weight: 4lb (1.9kg)

Operating Temperature: 32° – 122°F (0 – 50)°C

COMPATIBILITY



iOS iPhone and iPad

Android Phone and Tablet

Mac and Windows