

22LJ4540

22" IPS Full HD TV

22"

* Class size: See below for details.

22-inch (1720x1080) TV

Full HD IPS

Triple XD Engine

Eye Comfort Mode

Smart Energy Saving



PICTURE QUALITY	
Screen Size	21.5" / 55cm
Resolution	1920x1080
Panel Type	Wide Viewing Angle (IPS)
Color Gamut (CIE1931)	68%
Color Bit	8bit (6bit+FRC)
Color Depth (Number of Colors)	16.7M
Pixel pitch(mm)	0.24795x0.24795
Brightness (Typ.)	180 cd/m2
Contrast Ratio (Original)	1000:1
Contrast Ratio (DFC)	5M:1
Response Time_Typ. (GTG)	14ms
Viewing Angle (CR≥10)	R/L 178 (Typ.), U/D178 (Typ.)
Surface Treatment(Glare/non Glare)	non Glare
INPUTS / OUTPUTS	
HDMI	1 EA, HDMI 1.3
TUNER INPUT	
Digital	ATSC
Analog	NTSC
SPEAKER	
Type	Internal
Audio output	3W x 2
POWER	
Type (w/ Watt)	Adapter (24W)
Input	100-240V
Normal On(Typ.)	2W
Power Save/Sleep Mode(Max)	1W
DC Off(Max)	0.5W

FEATURES	
HDCP	Yes
Remote Control	Yes
Caption	Yes
Flicker Safe	Yes
Eye Comfort Mode	Yes
Smart Energy Saving	Yes
Motion Eye Care	Yes
Auto / Manual Clock	Yes
On/ Off Time	Yes
Sleep Timer	Yes
Auto Off / Auto Sleep	Yes
Picture Mode	Vivid/ Standard/ APS/ Cinema/Sport/Game/Expert1/ Expert2
Triple XD engine	Yes
ARC-PC	16:9, 4:3
ARC-Video	16:9 - DTV, ATV, HDMI Just Scan - DTV, HDMI (720p↑) Original - DTV, ATV, HDMI Full Wide - DTV, ATV 4:3 - DTV, ATV, HDMI 14:9 - DTV, ATV, HDMI Zoom - DTV, ATV, HDMI Cinema Zoom - DTV, ATV, HDMI
WALL MOUNT	
VESA	75x75
STANDARD	
UL / cUL	Yes
FCC-B	Yes
EPA	Yes
ACCESSORY	
Remote Controller	Yes
DIMENSIONS/ WEIGHTS	
Product with Stand (WxHxD)	20.0" x 5.8" x 14.1
Product without Stand (WxHxD)	20.0" x 2.1" x 12.5"
Shipping Size (WxHxD)	26.0" x 15.0" x 5.0"
Product Weight with Stand	6.6 lbs
Product Weight without Stand	6.4 lbs
Shipping Weight	9.3 lbs
LIMITED WARRANTY / UPC	
Limited Warranty	1 Year Parts and Labor
UPC	719192608979
Country of Origin	Mexico

HOME ENTERTAINMENT