


iQ500 WM14T391GB Front loading automatic washing machine



A+++



iSensonic Washing Machine with iQDrive for highly effective and efficient laundry care with large easy-to read display.

- ✓ Intelligent, durable and quiet iQdrive motor with 10-year warranty for highly effective and efficient laundry care.
- ✓ With the option speedPerfect, get perfect washing results in up to 65% less time.
- ✓ Sensor-controlled wash programmes for the most efficient water usage with any load size - thanks to the water management system.
- ✓ A+++ -30%: washes 30% more efficient than the requirement for energy efficiency class A+++.
- ✓ Super Quick 30/15 washes, rinses and spins in just 30 minutes, if required in 15 minutes also.

Features

Technical Data

Installation type : Freestanding
 Height of removable worktop (mm) : 850
 Dimensions of the product (mm) : 848 x 598 x 550
 Net weight (kg) : 70.0
 Connection rating (W) : 2300
 Current (A) : 10
 Nominal power (kW) : 220-240
 Frequency (Hz) : 50
 Approval certificates : CE, VDE
 Length of electrical supply cord (cm) : 210
 Washing performance class : A
 Door opening : Left
 Wheels : No
 EAN code : 4242003792377
 Capacity (kg) : 8.0
 Energy efficiency : A+++ : exceptionally efficient
 Energy consumption annual (kWh/annum) - NEW (2010/30/EC) : 135
 Power consumption in off-mode (W) - NEW (2010/30/EC) : 0.12
 Power consumption in left-on mode - NEW (2010/30/EC) : 0.58
 Water consumption annual (l/annum) - NEW (2010/30/EC) : 9680
 Spin drying performance class : B
 Max. spin speed (rpm) : 1400
 Average washing time cotton 40C (partial load) - NEW (2010/30/EC) : 224
 Average washing time cotton 60C (full load) (min) - NEW (2010/30/EC) : 224
 Average washing time cotton 60C (partial load) - NEW (2010/30/EC) : 224
 Duration of the left-on mode - NEW (2012/30/EC) (min) : 15
 Noise level washing (dB) : 51
 Noise level spinning (dB) : 77
 Installation type : Freestanding



iQ500

WM14T391GB

Front loading automatic washing machine

Features

- iQdrive, Extraklasse

Performance

- Energy efficiency class: A+++
- Capacity: 8 kg
- Maximum spin speed: 1400 rpm
- B spin class
- Energy consumption :135 kWh per year, based on 220 standard washing cycles
- -30% more economical (135kWh/year) than the standard value (217 kWh/year)
- Energy consumption: standard 60 °C cotton programme 0.77 kwh full load and 0.54 kwh partial load and 40 °C cotton programme 0.4 kwh partial load
- Water consumption 9680 litres per year, based on 220 standard washing cycles
- Cottons 60 Eco and Cottons 40 Eco are the standard washing programmes to which the information in the label relates. These programmes are suitable to clean normally soiled cotton laundry and are the most efficient programmes in terms of combined energy and water consumption.
- Programme time:60 °C cotton programme 224 min at full load 224 min at partial load and 40 °C cotton programme 224 min partial load
- Duration of the left-on mode: 15 min
- Drum volume: 65 litres
- Weighted power consumption off-mode / left-on mode: 0.12 W / 0.58 W
- Noise level washing : 51dB (A) re 1pW: Noise level spinning:77dB (A) re 1 pW
- Noise level spinning:77dB (A) re 1 pW:

Programmes/functions

- Fully electronic control dial for wash programmes, temperature and special programmes
- Special programmes: jeans, mixed fabrics, hygiene, rapid 15 minute quick wash, , delicates/silk programme
- Touch control buttons: start/pause with reload function, spin speed selection, Water & Rinse Plus, speedPerfect/ecoPerfect and 24 hours time delay

Key features

- varioPerfect:speed or energy efficiency with perfect wash performance every time
- waterPerfect Plus: water management system
- antiVibration Design - for more stability and quietness
- Reload function: Pause the already running washing machine to add any forgotten items of laundry to the drum.

Additional features

- iQ Drive:innovative motor technology delivering energy efficiency,speed and durability
- Large LED-Display for programme status indication, temperature selection, spin speed, remaining time and 24 hours end time delay, load recommendation and consumption indication
- waveDrum - Gentle washing thanks to a unique drum structure
- Time delay 24 hours and time remaining indicator
- autoLoad Plus
- Multiple water protection
- Electronic child safety package
- Self cleaning detergent dispenser
- Flow-through sensor for optimum water use
- Foam detection system
- Out of balance load adjustment

Technical Information

- Dimensions (H X W X D): 84.8 x 59.8 x 55 cm
- Slide-under installation
- integrated 32 cm porthole, Alu-Look, white with 171° opening door

iQ500
WM14T391GB
Front loading automatic washing
machine

Dimensioned drawings

