

iQ300
SN236W00IG white
Dishwasher 60cm
Freestanding ,



A++



- ✓ Up to 66% faster dishwashing and drying to a gleaming shine with varioSpeed Plus.
- ✓ At the press of a button, the autoProgramme controls the entire dishwashing process for brilliant results.
- ✓ Very efficient dishwashing in energy efficiency class A++.
- ✓ aquaStop for a lifetime guarantee against water damage.

Features

Technical Data

Cleaning performance : A
 Water consumption (l) : 9.5
 Total annual energy consumption (kWh) 220 days : 202
 Total annual water consumption (l) 220 days : 2090
 Construction type : Free-standing
 Removable work top : Yes
 Door panel options : Not possible
 Height of removable worktop (mm) : 815
 Height of the product (mm) : 845
 Adjustable feet : Yes - front only
 Maximum adjustability feet (mm) : 20
 Adjustable plinth : No
 Net weight (kg) : 47.0
 Gross weight (kg) : 52.0
 Connection rating (W) : 2400
 Current (A) : 13
 Voltage (V) : 220-240
 Frequency (Hz) : 60; 50
 Length of electrical supply cord (cm) : 175
 Plug type : GB plug
 Length inlet hose (cm) : 165
 Length outlet hose (cm) : 190
 Hidden heating element : Yes
 : Button suspension, Childlock appliance
 Water softener (kWh) : Yes
 Adjustable upper basket : Rackmatic 3-stage
 3rd Rack : None
 Silverware Basket : Standard
 Optional accessories : SZ72010, SZ73001, SZ73100, SZ73300, SZ73640
 Included accessories 2 : baking-sheet spray head grey
 Number of place settings : 13
 Color / Material body : White
 Color / Material top : White
 Brand : Siemens
 Product name / Commercial code : SN236W00IG
 Number of place settings : 13
 Energy efficiency class - NEW (2010/30/EC) : A++
 Energy consumption annual (kWh/annum) - NEW (2010/30/EC) : 262
 Energy consumption (kWh) : 0.92
 Power consumption in left-on mode (W) - NEW (2010/30/EC) : 0.10
 Power consumption in off-mode (W) - NEW (2010/30/EC) : 0.10
 Water consumption annual (l/annum) - NEW (2010/30/EC) : 2660
 Drying performance : A
 Reference programme : Eco
 Total cycle time of reference programme (min) : 210
 Duration of the left-on mode - NEW (2012/30/EC) (min) : 0
 Noise level (dB(A) re 1 pW) : 46
 Installation type : Built-under
 Panel ready : No
 Connection rating (W) : 2400
 Current (A) : 13
 Voltage (V) : 220-240
 Frequency (Hz) : 60; 50
 Energy Star Qualified : No
 NSF certified : No
 Plug type : GB plug
 Required cutout/niche size for installation (in) : x x
 Dimensions of the packed product (in) : 34.64 x 26.37 x 26.77
 Net weight (lbs) : 103

iQ300
SN236W00IG white
Dishwasher 60cm
Freestanding ,

Features

Performance

- Energy Efficiency Class: A++
- Capacity: 13 place settings
- Energy consumption in Eco 50 programme: 262 kWh per year, based on 280 standard cleaning cycles
- Water consumption in Eco 50 programme: 2660 litres per year, based on 280 standard cleaning cycles
- Programme time in Eco 50 programme: 210 minutes
- A rated performance for washing and A for drying
- Noise level dB (A) re 1pW: 46 dB
- Noise level (silence programme): not available(A) re 1 pW
- Power consumption off-mode / left-on mode: 0.1 W / 0.1 W

Programmes/functions

- 6 programmes:
Intensive 70 °C, Auto 45-65 °C, Eco 50 °C,
Glass 40 °C, Quick wash 45 °C, Pre-Rinse
- 3 special options: varioSpeed Plus, halfLoad, extraDry
- Machine Care - 30 cycle reminder to run cleaning programme

Flexible design elements

- varioFlex baskets
- 3 stage rackMatic height-adjustable top basket
- 2 foldable plate racks in top basket
- 4 foldable plate racks in bottom basket

Innovations and technology

- hydroDry hygienic and efficient drying
- dosageAssist detergent dispenser
- iQDrive motor
- Automatic detergent-aware system
- hydroSensor, loadSensor

Design features

- Time delay: 1-24 hours with Remaining programme time indicator (minutes), water inlet indicator
- Internal water protection system
- LED salt refill indicator, LED rinse aid refill indicator
- Self-cleaning filter system with 3 piece corrugated filter
- Child safety - childproof door lock, Child safety - Tamperproof controls
- Dimensions (HxWxD): 84.5 x 60 x 60cm
- Efficiency information relates to the Eco 50 programme. This programme is suitable for cleaning normally soiled tableware and is the most efficient programme in terms of combined energy and water consumption.