

# WF2409E

300Mbps Wireless N Router



*Easy Network, Trustable*

## OVERVIEW:

The new netis router WF2409E offers 300Mbps high speed to connect your computers, smartphones, wireless cameras and other Wi-Fi devices. Equipped with three 5dBi high gain antennas, it ensures a better wireless coverage and allows you to enjoy the wireless freedom anywhere around your home, ideal for faster downloading, Internet calling and HD video streaming.

## KEY FEATURES:

- Incredible wireless high speed up to 300Mbps, great for faster downloading, Internet calling and HD video streaming
- Three MIMO high-gain 5dBi antennas providing maximum range and stable connections
- Various WAN connection types in AP Router mode: DHCP, Static IP, PPPoE, WISP, L2TP, PPTP, Dual Access (Russia PPPoE/PPTP/L2TP)
- Guest Network provides clients with separate visits while protecting the family network
- Intelligent bandwidth control to manage the bandwidth usage
- Internet Access Control- IP filtering, MAC Filtering, Domain Filtering based on time
- Quick setup, with built-in multilingual management page
- Support IPv6
- Support TR069
- Easy Setup with APP

## SPECIFICATION:

WIRELESS	
Standards	IEEE802.11b, IEEE802.11g, IEEE802.11n
Signal Rate	Up to 300Mbps
Frequency Range	2.4-2.4835GHz

Transmit Power	802.11n:40MHz(300Mbps,270Mbps,240Mbps,180Mbps,120Mbps,90Mbps,60Mbps,30Mbps);20MHz(144Mbps,130Mbps,115Mbps,86Mbps,57Mbps,43Mbps,28Mbps,14Mbps)(Auto-Sense) 802.11g:(54Mbps,48Mbps,36Mbps,24Mbps,18Mbps,12Mbps,11Mbps,9Mbps,6Mbps) 802.11b:(11Mbps,9Mbps,6Mbps,5.5Mbps,2Mbps,1Mbps)
Working Modes	Router,WISP,Access Point,Range Extender
<b>HARDWARE</b>	
Standards	IEEE 802.3 10Base-T,IEEE 802.3u 100Base-TX
Interface	1 * 10/100Mbps Auto MDI/MDIX RJ45 WAN port 4 * 10/100Mbps Auto MDI/MDIX RJ45 LAN ports
Antenna	3 * 5dBi Fixed Antenna
LED	PWR,WLAN,LAN1-LAN4,WAN,WPS
Buttons	WPS/Default
Power	DC 12V/0.5A(Output)
<b>SOFTWARE</b>	
WAN Type	DHCP,Static IP,PPPoE,L2TP,PPTP,Dual Access,WISP
Port Forwarding	Virtual Servers,Port Triggering,UPnP,DMZ,FTP Private Port
QoS	WMM,Bandwidth Control
Access Control	IP/MAC/Domain/IPv6 filtering
VPN Pass-through	PPTP,L2TP,IPSec
IPTV	Bridge,Tag VLAN
Dynamic DNS	Support
TR069	Support
Advanced	IGMP Proxy,IGMP Snooping,VPN,WOL,ARP List,Static Routing,Port Setting,Port Mirror,Remote Access,Backup & Restore,Firmware Upgrade
<b>PHYSICAL</b>	

Package Contents	1 * device 1 * 12V/0.5A Power Adapter 1 * Quick Installation Guide(Multilingual)
<b>OTHER</b>	
System Requirements	Internet Explorer 11+,Firefox 12.0+,Chrome 20.0+,Safari 4.0+, or other JavaScript-enabled browser Cable Subscription with an internet service provider (for internet access)
Certifications	FCC,CE
Environment	Operating Temperature: 0°C~40°C ( 32°F ~104°F ) Storage Temperature: -40°C~70°C (-40°F ~158°F ) Operating Humidity: 10%~90% non-condensing Storage Humidity: 5%~90% non-condensing

