

GCS1902

## 2-Port DisplayPort KVMP Switch with USB 3.0 Hub (TAA Compliant)



- Switch between two computers with the push of a button
- Stunning 4K video resolution
- Multiple switching options - via pushbutton, hotkey, or mouse
- 2 x USB 3.0 built-in ports for peripheral sharing
- Cost effective: Cables included, firmware upgradable
- Plug-N-Play

### 2-Port DisplayPort KVMP Switch

IOGEAR's 2-Port DisplayPort KVMP Switch features the most affordable combination of 4K UHD resolution, the next generation USB3.0 hub, and enhanced user-friendly operation. Experience 3840x2160 @ 30Hz resolution while switching between two computers and share two USB peripherals with the push of a button. Control two DisplayPort computers with ease using a single keyboard, mouse, and DisplayPort monitor. Expand your USB 3.0 peripherals connectivity with faster data transfer rates and eliminate redundant hardware.

- Control 2 computers using a single keyboard, mouse, and DisplayPort video console
- Superior video quality – 4K UHD (3840x2160 @ 30Hz)
- DisplayPort 1.1 compliant & HDCP compliant
- 2-Port USB 3.0 Hub with SuperSpeed 5Gbps transfer rate
- Dual-Mode DP supports HDMI and DVI output<sup>1</sup>
- Computer selection via front panel pushbuttons, hotkeys, and mouse<sup>2</sup>
- Independent switching of the KVM, USB, and audio
- Supports HD audio through DisplayPort<sup>3</sup>
- Full bass response for high quality 2.1 channel audio
- Mouse emulation or bypass feature supports most mouse drivers and are unsure of the video source's DP++ compatibility multifunction mice
- Multi-platform support – Windows®7, Windows®8.1, Windows®10, Mac®, and Linux®

- Multilingual keyboard mapping supports English, Japanese, French, and German keyboards
- Mac® keyboard support and emulation<sup>4</sup>
- Auto Scan Mode to monitor all computers
- Power On Detection
- Hot pluggable
- Firmware Upgradable


<sup>1</sup> Dual-Mode DisplayPort (DP++) does not require an active adapter for most single display setups. Active DisplayPort adapters are recommended if you

<sup>2</sup> Mouse port switching supported alongside mouse emulation mode using a USB 3-button mouse wheel

<sup>3</sup> HD audio through DisplayPort cannot be switched independently

<sup>4</sup> PC keyboard combinations emulate Mac® keyboards. Keyboards only work using their own Operating System





### Requirements

- **Console:**
  - DisplayPort compatible monitor
  - Standard 104 key wired USB keyboard
  - Standard 2 or 3 button wired USB mouse
  - Speakers (optional)
  -
- **Computers:**
  - DisplayPort port
  - USB Type-A port
  - Audio ports (optional)
  -
- **Cables:**
  - Use only specifically designed IOGEAR DisplayPort KVM Cable sets included

### Package Contents

- 1 x GCS1902
- 2 x DisplayPort cables
- 2 x USB 3.0 cables
- 2 x Audio cables
- 1 x Power adapter
- 1 x Manual

\*Use with video adapter may change performance

## Specifications

Function	GCS1902	Dimensions	GCS1902
<b>Computer Connections</b>			
Direct	2	Height	2.94" (7.47cm)
<b>Port Selection</b>			
	Pushbutton, Hotkeys, Mouse (mouse port switching only works with 3-key USB mouse wheel in emulation mode)	Depth	1.69" (4.29cm)
<b>Console Connectors</b>			
Monitor	1 x DisplayPort	Length	7.875" (20cm)
Keyboard	1 x USB 3.0 Type A	<b>Unit Package Dimensions</b>	
Mouse	1 x USB 3.0 Type A	Width	11.25" (28.58cm)
Audio	2 x 3.5mm Mini Stereo Jack (Front and Rear)	Height	6.81" (17.3cm)
<b>CPU Connectors</b>			
Monitor	2 x DisplayPort	Depth	4" (10.16cm)
Audio	2 x 3.5mm Mini Stereo Jack	<b>Master Carton</b>	
Keyboard & Mouse	2 x USB 3.0 Type B	Width	12.5" (31.75cm)
<b>Switches</b>			
F/W Upgrade	1 x USB Type B	Height	14.75" (37.47cm)
Port Selection	2 x Pushbutton	Depth	12" (30.48cm)
<b>Power Connections</b>			
	1 x DC 5V Jack	Master Carton Qty.	6
<b>Connectors</b>			
USB	2 x USB 3.0 Type A (Front and Rear)	<b>Weight</b>	
<b>LEDs</b>			
Mode	2 x Orange	Master Carton Wt.	24.7lb (11.24kg)
On Line	2 x Green	Unit Pack Wt.	3.68lb (1.67kg)
KVM	2 x Orange	Unit Wt.	1.45lb (0.66kg)
Audio	2 x Orange		
USB Peripherals	2 x Green		
<b>Emulation</b>			
Keyboard	USB		
Mouse	USB		
<b>Video Resolution</b>			
	2560 x 1600 @ 60Hz, 3840 x 2160 @ 30Hz (4K UHD)		
<b>Scan Interval</b>			
	1~99 seconds (5 seconds default)		
<b>Power</b>			
Voltage	DC 5V		
Amps			
<b>Environment</b>			
Operation Temperature	0~50C		
Storage Temperature	-20~60C		
Humidity	0~80% RH, Non-condensing		
<b>Housing</b>			
Case	Metal		