

# SPEC SHEET



## 1 FT HIGH SPEED HDMI® CABLE WITH ETHERNET

SUPPORTS HDR, 18GBPS, 4K@60Hz



- FULL 18GBPS BANDWIDTH
- ULTRAHD, 4K@60Hz, 4:4:4 CHROMA SAMPLING
- ENABLES TRANSMISSION OF HIGH DYNAMIC RANGE (HDR) VIDEO
- EMI TESTED TO ENSURE CABLES MINIMIZE INTERFERENCE WITH WIRELESS SIGNALS
- 100% ALUMINUM SHIELDED CONNECTOR, 360 DEGREES OF COVERAGE
- 32 AUDIO CHANNELS WITH ARC
- FUTURE-PROOFED AND PERFECT FOR TODAY'S 4K/ULTRAHD ENVIRONMENT
- CL3 RATED FOR IN WALL NON-PLENUM INSTALLATIONS

PART #: 0E-HDMIP1  
UPC: 811914027485  
LENGTH: 1 FT.  
WEIGHT: .24 LBS

CABLE CONSTRUCTION	28 AWG
JACKET OUTER DIMENSION	7.3 MM
MINIMUM BEND RADIUS	60 MM
MAXIMUM COLOR DEPTH	48-BIT, 16 BITS PER COLOR
MAXIMUM REFRESH RATE	4K 60 HZ + HDR
HDMI HIGH SPEED	YES
ETHERNET	YES
AUDIO RETURN CHANNEL	YES
DEEP COLOR SUPPORT	YES
3D COMPATIBLE	YES
4K SUPPORT	YES
AUDIO SUPPORT	DTS-HD DOLBY TRUEHD, ATMOS
RATINGS/CERTIFICATIONS	ROHS, UL LISTED, CL3 RATED
WARRANTY	LIMITED LIFETIME

Product Certification:



FOR MORE INFORMATION,  
CONTACT YOUR ADI SALES PERSON.

wboxtech.com