

QCA8075B

| | |
|-----------------------------|------------------|
| Camera Type | Bullet |
| Camera Technology | Analog HD |
| Image Sensor Size | 1/3" 4 Megapixel |
| Image Sensor Type | CMOS |
| Image Resolution | 4MP |
| Megapixels (digital) | 4 |
| Effective Pixels | 2688 x 1520 |
| Lens Size | 3.6mm |
| Angle of View | 84.8° |
| IR Cut Filter | Yes |



NIGHT VISION

| | |
|----------------------|-------------------------------------|
| IR LEDs | 18 |
| Infrared Wavelength | 850nm |
| Min Lux Illumination | 0.03 Lux/F2.0 (AGC on), 0 Lux IR on |
| Night Vision Range | Up to 98 ft |

ADDITIONAL IMAGE FEATURES

| | |
|------------------------|---|
| Auto Iris | No |
| On Screen Display | Yes |
| Backlight Compensation | Yes |
| Electronic Shutter | PAL 1/25~1/100,000s NTSC: 1/30~1/100,000s |
| Gain Control | Auto |
| Wide Dynamic Range | DWDR |
| Noise Reduction | 2D |

REMOTE MONITORING

| | |
|---------------------------|---------------------------------|
| Use as Standalone | No |
| Compatible Mobile Devices | Depends on the DVR connected to |
| Compatible Systems | QC968 / QC9616 |

PHYSICAL ATTRIBUTES

| | |
|----------------------------|-----------------------------|
| Weatherproof | Yes |
| IP Rating | IP67 |
| Body Construction | Aluminium |
| Mounting Hardware | Screws |
| Weight | 12.4 oz |
| Dimensions without bracket | 6.48" w x 2.76" d x 2.82" h |
| Operating Temperature | -40° to 140° F |

PTZ

| | |
|----------------------------|----------------|
| Horizontal Rotation | Not applicable |
| Vertical Tilt | Not applicable |
| Preset and Cruise Patterns | Not applicable |

AUDIO

| | |
|------------------|----------------|
| Audio Range | Not applicable |
| Audio Microphone | Not applicable |

CONNECTIVITY

| | |
|-------------------|-------------|
| Connector Types | BNC |
| Other Connections | 2.1mm power |
| Wireless | No |

POWER

| | |
|-------------------|-----------|
| Power Supply | 12V |
| Power Consumption | Max. 5.9W |