

# ZBOX MI526

**SKU:** ZBOX-MI526-BE/J/U/K/AUS

Raise productivity to a whole new level with Intel 7th Generation Kaby Lake processing power. This Mini PC has enough power for compiling complicated codes while maintaining native 4K output. With efficient power and thermal management, the Mini PC performs with minimal carbon footprint. Whether it is home, office or even at the lab, this Mini PC is the perfect suit.



ULTRA HD



802.11 AC WiFi



HD AUDIO



SDXC CARD READER



DUAL GIGABIT LAN



## TECHNICAL SPECIFICATIONS

### AIR COOLED

#### FEATURES

- Intel Clear Video HD technology
- Intel Quick Sync Video technology
- Native 4K output
- Microsoft DirectX 12 compatible
- 802.11ac WiFi & Bluetooth 4.2

#### SPECIFICATIONS

- Intel HD Graphics 620
- Intel i3-7100U Processor (dual-core 2.4 GHz)

#### AUDIO OUTPUTS

- Digital 8 Channel Loss-less Bitstream (via HDMI)
- Analog Stereo In / Out

#### SOFTWARE COMPATIBILITY

- Microsoft Windows 10 64-bit

#### HARD DRIVE & MEMORY

- 1 x 2.5-inch SATA 6.0 Gbps HDD/SSD
- 2 x 260-pin DDR4-1866/2133 SODIMM Slot (up to 32GB)

#### REAR PORTS

- WiFi antenna connector
- 1 x USB 2.0, 2 x USB 3.0
- 2 x 10/100/1000 Ethernet (RJ45)
- Power connector

#### INSIDE THE BOX

- ZOTAC ZBOX MI526
- Power adapter and cable
- VESA monitor mount (w/4 screws)
- WiFi antenna
- USB Flash Drive with OS drivers
- Support DVD
- User Manual
- Quick Guide

#### FRONT PORTS

- Power Button
- 3-in-1 card reader (SD/SDHC/SDXC)
- USB 3.0 port Combo
- 2 x USB 3.1 Type-C, 1 x USB 3.0
- WiFi LED
- Hard drive LED
- Power LED

#### TOP PORTS

- 1 x USB 3.0

#### DISPLAY OUTPUTS

- HDMI 1.4 (3840x2160 @ 30Hz), HDCP compliant
- DisplayPort 1.2 (3840x2160 @ 60Hz)

#### MINI PC DIMENSIONS

- Length: 188mm (7.4in)
- Width: 188mm (7.4in)
- Height: 44mm (1.73in)

#### BOX DIMENSIONS

- Length: 330mm (12.99in)
- Width: 325mm (12.80in)
- Height: 83mm (3.27in)



For more information please visit:  
**ZOTAC.COM**

\*Extended warranty exclusions may apply based on country/region.

©2016 ZOTAC International (MCO) Ltd. All rights reserved. All company and/or product names may be trade names, trademarks and/or registered trademarks of the respective owners with which they are associated. Features, pricing, availability and specifications are subject to change without notice. ZOTAC International (MCO) Limited does not warrant the accuracy, completeness or reliability of information, materials and other items contained on this website or server. No liability is assumed with respect to the use of the information contained herein. When accessing this website, users acknowledge that ZOTAC International (MCO) Limited will not be liable in any event for any damages arising out of the use of this site or any websites linked to it.