

P2-A

SMART PICO PROJECTOR



Truly **Portable**, Truly **Pico**

Wireless Entertainment Anytime, Anywhere

The P2-A is the best-value wireless pico projector with Android™ on the market. There are no tradeoffs and no compromise - simply value. Featuring best in class resolution, the P2-A offers a host of other features including onboard media player, HDMI and Composite Video input, and 150 minute battery life.



**Android™
Lollipop 5.1**



**150 Minute
Battery**



**Wireless
Projector**



**Small &
Portable**



**150 Lm Optical
Engine**



**Smartphone
Mirroring**

PROJECTION SYSTEM

Max Resolution: 1920x1080 (1080p)
Native Resolution: 854x480 (WVGA)
Max Brightness (DC): 130 Lumens
Contrast Ratio: 1000:1
Projection Lens: Manual Focus
Projection Image Size: 8"-100"
Lamp: Triple RGB LEDs with Vibrant Color Technology - Life 20,000hrs



INPUTS / OUTPUTS

Video In: Mini Digital AV
Composite A/V (3.5mm Jack)
Audio Out: 3.5mm Stereo Headphone
Jack
USB: Full Sized USB 2.0

ANDROID SYSTEM

Processor: Quad-Core ARM Cortex 1.3 ghz
Android Operating System: 5.1.1 Lollipop
RAM: 1GB
Memory: 8GB
WiFi: 802.11 b/g/n
Bluetooth: 2.0 Compatible

THROW RATIO

Throw Ratio: 1.2
Projection Offset: 100%



GENERAL SPECIFICATIONS

Battery Runtime: 150 Minutes (Eco Mode)
Audio Output: 1W Speaker Stereo speaker/
headphone mini-jack
Color: White
File Playback: MicroSD & USB Host reader
Menu Language: English, Spanish, French,
Chinese (Traditional/Simplified), Dutch, Korean,
& Japanese
Aspect Ratio Control: 16:9
Dimensions: 2.9" x 2.9" x 2.4"
Weight: 0.55 lbs
Power Consumption: 11 Watts
Supported Formats: MP3 / WMA / OGG / WAV /
AVI / BMP / JPG / GIF / TXT
Conformances: CE, FCC Class A



Photos



Videos



Music



Settings



Text



Inputs



INCLUDED ACCESSORIES

Remote Control, Composite AV Cable,
USB Charging Cable, Tripod, User Manual