

GUC211V

Portable Laptop Console Crash Cart Adapter (TAA Compliant)




- Diagnose and troubleshoot computers quickly from your laptop
- Perfect for: Data centers, IT departments, refurbishing centers or kiosk services
- Plug-N-Play - No software needed
- Programmable hotkeys and macros
- Best value for reducing labor and hardware costs

USB Console to Laptop Crash Cart Adapter

IOGEAR's Portable Laptop Console Crash Cart Adapter provides instant computer access through your laptop. Simply connect the crash cart adapter to your target computer, kiosk, or server from your laptop, run the executable file, and you are good to go! Save time by programming hotkeys and macros for common tasks and avoid the hassle of lugging around unneeded equipment. This one-to-one solution is the perfect accessory for any IT professional.

- Provides direct Laptop-to-Computer desktop access
 - Programmable macros and hotkeys
 - Plug-N-Play - No additional software needed
 - Bi-directional file transfer between connected laptop and computer
 - Access laptop applications in virtual window without switching windows
 - VGA - resolutions up to 1920x1200 @60Hz
 - Supports DisplayPort, HDMI, and DVI interface with IOGEAR's display adapters
 - BIOS level access
 - Perform OS patching, software installation and diagnostic testing on remote computer
 - Video recording and capture of remote computer*
 - Mouse DynaSync™ - automatically synchronizes the laptop and connected computer's mouse movements
 - On-screen virtual keyboard with multi-language support
 - Supports Windows® 2000, Window Vista®, Windows® 7, Windows® 8, Windows® 8.1, Windows® 10, Windows® 10.1
 - Adjust remote computer virtual window resolution
 - Hot-Pluggable
 - Firmware upgradable
- *Requires Java application v1.7.0_75 or later ready from laptop for video recording playback





Requirements

Package Contents

- | | |
|--|---|
| <ul style="list-style-type: none"> • Laptop: <ul style="list-style-type: none"> Hardware: <ul style="list-style-type: none"> USB 2.0 Port Operating Systems: <ul style="list-style-type: none"> Windows® 2000, Windows® Vista, Windows® 7, Windows® 8.1, Windows® 10 • Target Computer: <ul style="list-style-type: none"> Hardware: <ul style="list-style-type: none"> USB Type A Port VGA Port DisplayPort (with a dapter) HDMI Port (with a dapter) DVI Port (with a dapter) | <ul style="list-style-type: none"> • 1 x GUC211V Portable Laptop Console Crash Cart Adapter • 1 x USB Type A to USB Mini-B Cable • 1 x QSG |
|--|---|

Note:

The GUC211V only controls the connected computer through a direct cable connection. The GUC211V supports one-to-one direct KVM console; it cannot be used to control two stand-alone PCs, as it only provides one computer with desktop access. User must know login credential of the connected computer if needed for access.

Specifications

Function	GUC211V	Dimensions	GUC211V
Computer Connections		Unit Dimensions	
Direct	1	Height	2.375" (6.03cm)
CPU Connectors		Depth	0.75" (1.91cm)
Monitor	1 x VGA Male (Blue)	Length	2.18" (5.56cm); Mini to Type A USB Cable: 72" (183cm); USB and VGA Cables: 19" (48.26cm)
Keyboard & Mouse	1 x USB Type A Male (Black)	Unit Package Dimensions	
Console Connectors		Width	4.68" (11.9cm)
Keyboard, Mouse, and Monitor	1 x Mini-USB Female (Black)	Height	6.29" (16cm)
Video Resolution		Depth	2.3" (5.9cm)
1920x1200 @60Hz		Master Carton	
LEDs		Width	14.7" (37.5cm)
On Line	1 x Blue	Height	7" (17.8cm)
Environment		Depth	10" (25.4cm)
Operation Temperature	0~40C	Master Carton Qty.	12
Storage Temperature	-20~60C	Weight	
Humidity	0~80% RH, Non-condensing	Master Carton Wt.	8.15lb (3.7kg)
Housing		Unit Pack Wt.	0.39lb (0.18kg)
Case	Plastic	Unit Wt.	0.4lb (0.18kg)
Warranty			
3 Years			