


High-Speed HDMI Cable, Gripping Connectors, 4K @30Hz (M/M), White, 16 ft. (4.88 m)

MODEL NUMBER: **P568-016-WH**



Premium HDMI cable connects two 4K-enabled devices, including computers, Blu-ray™ players, video game systems, DVRs, video cameras, A/V receivers, monitors, projectors and televisions.

Description

The P568-016-WH High-Speed HDMI 4K Cable (M/M) is recommended for digital signage, video presentations, point-of-sale displays, classrooms and other applications that display Ultra High Resolution (UHD) video and multi-channel audio. It connects 4K-enabled source devices, such as computers and Blu-ray players, to 4K-enabled displays, such as monitors, projectors and televisions.

This cable supports video resolutions up to Ultra HD 4K x 2K (4096 x 2160) at 30 Hz and data transfer speeds up to 18 Gbps. When used with an Apple® digital AV adapter, it supports iPad2® video mirroring for playing games, watching videos or displaying presentations.

The 16-ft. (4.88 m) molded 30 AWG cable features premium foil and braid shielding to deliver reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Gold-plated white connectors provide maximum conductivity and minimize data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking. A flexible PVC jacket makes the HDCP Pass-Through cable easy to install in tight spaces.

Features

Connects HDMI Source to 4K TV, Projector or Monitor

- Ideal for digital signage, video presentations, point-of-sale displays, classrooms and other applications with 4K video and multi-channel audio

High Performance and Wide Compatibility

- Supports UHD video resolutions up to 4096 x 2160 (4K x 2K) @ 30 Hz
- Supports data transfer speeds up to 18 Gbps
- Complies with HDCP Pass-Through standards
- Supports iPad2 video mirroring when used with Apple digital A/V adapter
- Backward compatible with previous HDMI generations

Superior Quality Ensures a Flawless Signal

Highlights

- Supports UHD video resolutions up to 4096 x 2160 (4K x 2K) @ 30 Hz
- Supports data transfer speeds up to 18 Gbps
- Complies with HDCP Pass-Through standards
- Premium foil and braid shielding protects against EMI/RFI noise
- Gold-plated white connectors for optimal signal transfer

Package Includes

- P568-016-WH High-Speed HDMI 4K Cable (M/M), White, 16-ft. (4.88 m)



- Corrosion-resistant gold-plated white connectors for maximum conductivity and minimum data loss
- Fully molded 30 AWG construction with integral strain relief reduces stress and adds flexibility
- Premium foil and braid shielding for EMI/RFI noise protection
- Flexible PVC jacket easy to install in tight spaces

Specifications

OVERVIEW	
UPC Code	037332203526
Technology	HDMI
VIDEO	
Max Supported Video Resolution	4096 x 2160 @30Hz
PHYSICAL	
Color	White
Cable Length (ft.)	16
Cable Length (m)	4.9
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.27
Shipping Weight (lbs.)	0.60
ENVIRONMENTAL	
Operating Temperature Range	32 TO 113 F (0 TO 45 C)
Storage Temperature Range	-40 TO 176 F (-40 TO 80 C)
Operating Humidity Range	10 TO 85% RH
Storage Humidity Range	5 TO 90% RH
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>