



DATA SHEET

Polycom® EagleEye™ MSR Camera

High performance HD camera designed specifically for use with Microsoft Skype Room Systems

The Polycom® EagleEye™ MSR camera provides a best-in-class quality video collaboration experience for Polycom® MSR™ and other Microsoft-certified Skype Room Systems. Certified by Microsoft as a Skype Room System camera peripheral, Polycom EagleEye MSR delivers a premium HD video experience with a pan, tilt and 12x optical zoom capability suitable for medium and large sized meeting spaces.

High quality video experience that satisfies large meeting space needs

Polycom EagleEye MSR camera produces incredible details and natural colors in full 1080pHD, reducing strains of video meetings for all meeting participants. The EagleEye MSR camera covers a wide field of view of 72.5°, with the mechanical pan, tilt, and 12x zoom that can be controlled using a simple handheld remote, so that meeting participants sitting at the back of the room can be just as easily and clearly seen by others.

Polycom EagleEye MSR camera is one of the camera options supported by Polycom MSR Series, and provides excellent video experiences including:

- HD 1080p video at 30 frame per second
- Wide field of view (72.5° Horizontal, 44.8° Vertical Field of View) with +170° pan and 120° tilt
- 12x optical zoom
- Simple, easy to operate remote
- Home preset position to quickly set and recall the camera to home position
- USB 2.0 connection to the MSR Dock or other Skype Room System docks to maximize the cable length between the dock and the camera



Benefits

- Delivers a high performance collaboration experience and plug-and-play connectivity for Polycom MSR and other Skype Room Systems
- 12x optical zoom and wide viewing range with pan and tilt provide extra coverage without loss in quality—ideal for medium and large meeting rooms
- Built for utmost ease of use, the camera comes with a user-friendly, simplified remote

Polycom EagleEye MSR	
Camera Type	1/2.7" CMOS
H/V Resolution	1920 x 1080
Output	1080p30/25, 720p30/25, 960x540p30/25, 640x360p30
Lens Focal Length	f=3.5mm to 42.3mm
Lens F#	1.8-2.8
Zoom	12x optical
Focus	Auto
Horizontal Field of View	6.9° - 72.5°
Vertical Field of View	3.9° - 44.8°
Min. Illumination	0.5Lux @ (F1.8, AGC ON)
Exposure	Auto-iris, AGC
SNR	≥ 55dB
Pan range	+/- 170°
Tilt range	+90/-30°
I/O	USB 2.0
IR Detectors	✓
Power consumption	12v @ 1.5A power
Dimensions (W x H x D)	141.5 x 175.9 x 151.8 mm
Video system compatibility	Certified Skype Room System
Room Size	Small, medium, large
Warranty	One-year return to factory parts and labor

Need flexible financing?

Polycom **CAPITAL**
Collaborative Financing
www.polycom.com/polycom-capital

About Polycom

Polycom helps organizations unleash the power of human collaboration. More than 400,000 companies and institutions worldwide defy distance with video, voice and content solutions from Polycom. Polycom and its global partner ecosystem provide flexible collaboration solutions for any environment that deliver the best user experience and unmatched investment protection.

Polycom, Inc.
1.800.POLYCOM
www.polycom.com

Polycom Asia Pacific Pte Ltd
+65 6389 9200
www.polycom.com.sg

Polycom EMEA
+44 (0)1753 723282
www.polycom.co.uk

