

CLEAN SEAL WATERPROOF BACKLIT MEDICAL KEYBOARD WITH CONTACTLESS SMART READER

Model: SSKSV207GRC125

All-in-one Clean Seal Washable, Waterproof Backlit Medical Keyboards from Seal Shield. Keyboard with a natural look and feel that makes typing smooth and simple. Features backlit keys for non-intrusive visibility assistance in darker settings. 100% waterproof & dishwasher-safe keyboard is IPX8-certified, compatible with medical-grade cleaners & disinfectants. A built-in smart card reader enables non-touch access. Features convenient USB connection for easy plug-and-play.

FEATURES:



100% Waterproof & Dishwasher Safe



IP68-Certified



Gold Plated USB Quick Connect Cable with Seal Cap™



Backlit Keys for improved visibility in darker environments



Built-In Contactless Smart Reader



Laser-Etched Key Labels



Compatible with Hospital Cleaners & Disinfectants



SSKSV207GRC125

MEDICAL-GRADE CLEANING CAPABILITIES

- Dishwasher-Safe (Hot & Cold settings)
- Bleach compatible. Clorox® approved. (including Clorox HealthCare Products)
- Disinfectants & Sporicides (including Lysol® products EPA-certified to kill COVID-19)
- Solvents, Corrosives and Acids
- Alcohol and H. Peroxide



CLEAN SEAL WATERPROOF BACKLIT MEDICAL KEYBOARD WITH CONTACTLESS SMART READER

Model: SSKSV207GRC125

TECHNICAL DATA:

Compatibility:	Window [®] s, (USB Models)
Construction:	ABS Plastic (Standard Style), Laser Etched Keys
Key Layout:	104 US Language
Net Dimensions LxWxH:	18.07 x 6.85 x 1.38in (45.9 x 17.4 x 3.5cm)
Gross Dimensions:	18.74 x 7.76 x 1.75in (47.6 x 19.7 x 4.45cm)
Net Weight:	1.77 lb (0.802kg)
Gross Weight:	1.99 lb (0.906kg)
Cable Length:	6in (15cm) Quick Connect Cable 6ft
Connection Type:	Gold Plated USB (can support PS/2 technology)
Card Reader Type/Speed:	RFIDeas [™] pcProx Nano 125KHz Proximity, 125KHz
Supported Smart Cards:	HID [®] Prox, Indala [®] , EM 410x, AWID, CASI-RUSCO, Kantech ioProx(Cards other than HID Prox require Card Reader to be Specially Formatted)
Key Switch Force:	53 ± 7gf
Key Switch Life Cycle:	> 10 Million Keystrokes
Key Switch Type:	Membrane Key Switch with Tactile Feedback
Power Consumption:	100mA Max
Total Key Travel:	4.0 ± 0.2mm
Operating Voltage:	+ 5VDC ± 5%
EMI - RFI:	Conforms to FCC Rules for Class B Device
Approvals/Certifications:	FCC, IPX8



Copyright© 2020, Seal Shield, LLC. All rights reserved. All other trademarks and trade names are those of their respective owners.

Limited 2-Year Warranty