

TRIPP-LITE

Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

# 4-Port HDMI Splitter - 4K @ 60 Hz, HDCP 2.2, HDR, TAA

# MODEL NUMBER: B118-004-UHD-2









Transmits 4K audio/video signals from one HDMI source device to 4 HDMI displays at the same time.

#### **Features**

#### Transmits a 4K HDMI A/V Signal to 4 HDMI Displays Simultaneously

- Recommended for 4K digital signage in classrooms, churches, offices, restaurants, bars, trade shows, etc.
- Distributes A/V signals up to 15 ft. (4.6 m) when used with standard 28 AWG HDMI cable
- Supports UHD resolutions up to 4K @ 60 Hz for crystal-clear video
- Supports HDCP 2.2 and EDID compliant to ensure compatibility with latest A/V hardware
- Cascade up to 3 levels of splitters together to increase the number of connected monitors up to 64 Supports the Most Up-To-Date Features and Formats
- Supports High Dynamic Range (HDR) for richer contrast and expanded color accuracy
- Full 3D
- DTS-HD, Dolby TrueHD, Dolby Digital Plus and LPCM 7.1-channel surround sound audio
- 36-bit Deep Color (12 bits per channel)
- Video amplifier bandwidth of 600 MHz/6 Gbps per channel (18 Gbps total)
- Lip sync pass-through, xvYCC and x.vColor

## Easy to Use Almost Anywhere

- Plug-and-play operation with no software required for easy, immediate installation
- · Supports desktop use or wall-mounting using included hardware
- Power supply includes international plug adapters (North America, Europe, U.K. and Australia)
   TAA-Compliant
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

# **Specifications**

# **Highlights**

- Supports UHD resolutions up to 4K @ 60 Hz for crystal-clear video
- Distributes A/V up to 15 ft. when used with 28 AWG HDMI cable
- Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy
- Expand the number of connected displays, up to 64, by cascading up to 3 levels
- Plug-and-play operation with no software required for easy, immediate installation

#### Package Includes

- B118-004-UHD-2 4-Port 4K 3D HDMI Splitter
- External power supply (Input: 100–240V, 50/60 Hz, 0.35A;
   Output: 5V 2A)
- International plug adapters (North America, Europe, U.K. and Australia)
- Mounting hardware
- Owner's manual





OVERVIEW	
UPC Code	037332200655
AC Adapter	Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A, 4 ft
Technology	НОМІ
VIDEO	
Max Supported Video Resolution	4K @ 60Hz (3840 x 2160)
Max Supported Color Depth	36-bit Deep Color
HDR Support	Yes
3D Video Supported	Yes
AUDIO	
Audio Specification	DTS-HD, Dolby TrueHD, Dolby Digital Plus and LPCM 7.1 Channel Surround Sound
INPUT	
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
External Power Supply Plug(s)	NEMA 5-15P North America; CEE 7/16 Schuko; BS 1363 UK; AS/NZS 3112 Australia
Bus Powered	No
Product Length (in.)	5.039
Product Length (ft.)	0.419
POWER	
External Power Supply Input Specs (V / Hz / A)	100-240V, 50/60HZ, 0.35A
External Power Supply Output Specs (V / A)	5V / 2A
External Power Supply Cord Length (ft.)	4.0
External Power Supply Cord Length (m.)	1.2
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	CE; FCC; UL; cUL; TUV; CCC; PSE; C-Tick; GS; RoHS
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Green (Power), (x2) Orange (Signal)
PHYSICAL	
Color	Black
Included Mounting Accessories	Yes





Material of Construction	Metal	
Rackmountable	Yes	
Shipping Dimensions (hwd / cm)	5.51 x 21.41 x 16.41	
Shipping Dimensions (hwd / in.)	2.17 x 8.43 x 6.46	
Shipping Weight (kg)	0.63	
Shipping Weight (lbs.)	1.39	
Unit Dimensions (hwd / in.)	2.16 x 6.45 x 8.42	
Unit Packaging Type	Вох	
Unit Weight (kg)	0.09	
Unit Weight (lbs.)	0.198	
ENVIRONMENTAL		
Operating Temperature Range	32 to 104 °F (0 to 40 °C)	
Storage Temperature Range	5 to 122 °F (-15 to 50 °C)	
Relative Humidity	0% to 85% RH, Non-Condensing	
COMMUNICATIONS		
EDID Compatible	Yes	
CONNECTIONS		
Ports	4	
Side A - Connector 1	HDMI (FEMALE)	
Side B - Connector 1	(4) HDMI (FEMALE)	
Connector Plating	Nickel	
FEATURES & SPECIFICATIONS		
HDCP Specification	2.2	
Driver Required	No	
STANDARDS & COMPLIANCE		
Certifications	FCC, CE, ROHS	
WARRANTY		
Product Warranty Period (Worldwide)	3-year limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

https://www.tripplite.com/products/product-certification-agencies