

Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cat6a 10G Snagless Molded Slim UTP Ethernet Cable (RJ45 M/M), Black, 6 ft. (1.83 m)

MODEL NUMBER: N261-S06-BK











Small-diameter cable connects high-density network equipment, such as computers, servers, routers, printers, patch panels and switches. Recommended for reducing cable clutter in busy data centers.

Description

The N261-S06-BK Cat6a 10G Snagless Molded Slim UTP Network Patch Cable (M/M) is ideal for connecting network components like computers, servers, routers, printers, patch panels and switches in high-density data centers. Designed for fast transmission and excellent signal quality, this 6-ft. (1.83 m) black cable ensures peak performance throughout your local area network (LAN).

Manufactured from 28 AWG copper wire, the four-pair stranded UTP N261-S06-BK delivers Ethernet speeds up to 10 Gbps. Protected by a PVC jacket, this cable is more than 38% smaller in diameter than standard Cat6a cable, which increases airflow in tight spaces and makes it easier to install around corners and through cable management panels.

RJ45 male connectors are conducive to an accurate signal transfer, improving near-end crosstalk (NeXT) performance to 500 MHz. The snagless design protects the locking tabs against being damaged or broken off during installation. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking.

Each cable has been tested and certified using Fluke® test equipment. It supports IEEE 802.3af, is DTE power compliant and is compatible with T568A/T568B wiring.

Features

Recommended Solution for Your Cat6a High-Density Network Connections Ideal for connecting components like computers, servers, routers, printers, patch panels and switches in high-density data centers Designed for fast transmission and excellent signal quality Ensures peak performance throughout your LANS upports Ethernet speeds up to 10 Gbps

Special Slim DesignMore than 38% smaller in diameter than standard Cat6a cableIncreases airflow in tight spacesIncreased flexibility for installing around corners and through cable management panelsCuts down on bothersome cable clutter

Premium Construction for Superior PerformanceHigh-quality 28 AWG 4-pair stranded copper wireMinimal near-end crosstalk ensures a strong signalRugged PVC jacket stands up to long-term use Snagless RJ45 ConnectorsMolded snagless boots prevent locking tabs from damage during installationIntegral strain relief protects cable and connectors from stress and cracking

Tested and Certified Using Trusted Fluke EquipmentSupports IEEE 802.3afDTE power compliantCompatible with T568A/T568B wiring

Specifications

Highlights

- Over 38% slimmer than standard Cat6a cables
- Easy to route through cable management panels
- Supports Ethernet speeds up to 10 Gbps
- Snagless RJ45 design protects tabs from damage
- High-quality 28 AWG stranded copper wire

Package Includes

N261-S06-BK Cat6a 10G
 Snagless Molded Slim UTP
 Network Patch Cable (M/M),
 Black, 6-ft. (1.83 m)



OVERVIEW		
UPC Code	037332203908	
Technology	Cat6a	
PHYSICAL		
Color	Black	
Cable Shielding	UTP	
Cable Jacket Material	PVC	
Cable Outer Diameter (OD)	3.8mm	
Number of Conductors	4 Pair	
Conductor Material	Stranded Copper	
Conductor Gauge	28 AWG	
Wire Gauge (AWG)	28	
Cable Length (ft.)	6	
Cable Length (m)	1.8	
Cable Length (in.)	72	
Cable Length (cm)	182.9	
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 22.86	
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.00	
Shipping Weight (kg)	0.09	
Shipping Weight (lbs.)	0.20	
COMMUNICATIONS		
Bandwidth per TIA Standard	500 MHz	
Maximum Bandwidth as Tested	600 MHz	
Maximum Data Rate	10Gbps	
Network Speed	10Gbps	
CONNECTIONS		
Side A - Connector 1	RJ45 (MALE)	
Side B - Connector 1	RJ45 (MALE)	
Contact Plating	Gold	
Connector Type	Molded	
Wiring Configuration	EIA/TIA 568B	
FEATURES & SPECIFICATIONS		



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234

Cable Style	Unshielded; Slim; Molded	
SPECIAL FEATURES		
IP68 Rated	No	
Snagless Connector	Yes	
Antibacterial	No	
STANDARDS & COMPLIANCE		
Certifications	RoHS Compliant	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies