



Redefine realism

DELL ULTRASHARP 27 4K HDR MONITOR – UP2718Q



THE WORLD'S FIRST UHDA PREMIUM CERTIFIED HDR10 MONITOR¹

View, edit and create stunningly realistic images in HDR10.



SIT BACK. RELAX. CREATE.

Fits the way you work.



DELL PREMIERCOLOR

Tackle color-critical jobs with all the tools you need.



HIGHLY RELIABLE

World's number 1 monitor company.*

Redefine realism

DELL ULTRASHARP 27 4K HDR MONITOR – UP2718Q



CREATE YOUR MASTERPIECE

View lifelike colors, exceptional clarity and striking details.

- **Visuals that inspire:** Design and edit your best work yet on the world's first 27" 4K HDR monitor that meets HDR10 standards.¹
- **Realism like never before:** An incredible peak brightness of 1,000 nits (at least three times brighter than today's standard SDR displays) means you'll see the deepest blacks and brightest whites for impressive, true-to-life visuals.
- **Details even in the dark:** Whether you are working in the shadows or the light, you'll still see small details that would otherwise be lost without a high contrast ratio of 20,000:1 and 384 local dimming zones.
- **The video editor's choice:** Handle even the most color-critical post production editing like a pro with the Rec. 2020 color space.
- **Capture every nuance:** Experience four times more detail than Full HD with 3840 x 2160 Ultra HD 4K resolution.

SIT BACK. RELAX. CREATE.

Convenient connectivity, simple manageability and adjustability to fit the way you work.

- **Convenient connections:** Experience multiple plugin options with dual HDMI 2.0a for simple connectivity to HDR devices.
- **Simple manageability:** View applications between two PCs simultaneously on your screen and manage the content with only one keyboard and mouse with a convenient keyboard, video and mouse (KVM) feature.
- **Designed with you in mind:** No two people work the same — tilt, pivot, swivel and adjust the height to experience your ideal setup.

For more information
visit Dell.com/monitors

DELL PREMIERCOLOR — SUPERIOR COLOR PERFORMANCE

Exceptional tools for color professionals.

- **A broad, brilliant spectrum:** Dell PremierColor offers wide color coverage that meets major industry standards — 100% AdobeRGB, 100% sRGB, 100% Rec. 709, and 97.7% DCI-P3 and 76.9% Rec. 2020 — for immaculate, unwavering colors.
- **Extraordinary color depth:** Tremendous color detail with 1.07 billion colors (that's 64 times more color depth than standard monitors). Even in dark areas, you'll see better color gradation and precision in more shades.
- **Fine-tune with precision:** Customize color parameters to your preference using the Custom Color mode, SDK² or an optional X-rite iDisplay Pro colorimeter.³
- **Accurate color, out of the box:** Calibrated on AdobeRGB and sRGB to an accuracy of Delta-E < 2 with a factory calibration report that gives you the confidence that colors will be impressively accurate right from the start.

SUPERB RELIABILITY

Comes with Dell's high reliability promise.

- Dell monitors are #1 worldwide for 6 consecutive years (2013 to 2019)!*
- Enjoy peace of mind with Dell's Premium Panel Exchange⁴.
- Minimize downtime with Dell's Advanced Exchange Service.⁵ Upgrade to 24x7 specialized technical phone support with the Dell ProSupport option.⁶



ULTRA HD PREMIUM™ logo is a trademark of
UHD Alliance, Inc.

Features & Technical Specifications

DELL ULTRASHARP 27 4K HDR MONITOR – UP2718Q

Display

Model number

UP2718Q

Viewable image size (diagonal)

68.47 cm (27 inches)

Active display area

Horizontal
Vertical

596.74 mm (23.49 inches)
335.66 mm (13.21 inches)

Maximum resolution

3840 x 2160 at 60 Hz

Aspect ratio

16:9

Pixel pitch

0.1554 mm x 0.1554 mm

Pixels per inch (PPI)

163

Brightness (typical)

400 cd/m², 1,000 cd/m² (peak)

Color gamut (typical)

100% Adobe RGB, 100% sRGB, 100% Rec. 709, 97.7% DCI-P3, 76.9% Rec. 2020 (calibrated on AdobeRGB and sRGB to Delta-E < 2)

Color depth

1.07 billion colors

Contrast ratio (typical)

1000: 1 (typical), 20,000:1 (HDR)

Color calibration SDK software

Yes

Color calibration with Optional Colorimeter

Yes

Viewing angle (typical) (vertical/horizontal)

178°/178°

Response time (typical)

6ms (gray to gray)

Panel technology

In-Plane Switching; Anti-glare treatment of the front polarizer (3H) hard coating

Backlight

LED

Dell Display Manager

Yes with Dell Easy Arrange, Input Manager and other key features

Picture-in-picture, Picture-by-picture

Yes

Remote asset manager

Yes, via Dell Command |Monitor

Operating system support

Windows 10, 8.1, 7

Connectivity

Connectors

1 x DP (ver 1.4), 1 x mDP (ver. 1.4), 2 x HDMI (ver. 2.0a), 2 x USB 3.0 upstream ports, 4 x USB 3.0 downstream ports (including 2 x USB 3.0 BC1.2 charging port), Audio line-out

Built-in devices

USB 3.0 super-speed Hub (with 2 x USB upstream port, 4 x USB 3.0 downstream ports, including 2 x USB 3.0 BC1.2 charging port at 2A max.)

Design features

Stand

Yes (tilt: 5°/21°, swivel: 45°/45°, pivot and height-adjustable)

Security

Security lock slot (security lock not included), anti-theft stand lock slot (to panel)

VESA mounting support

100 mm x 100 mm

Power

AC input

100 VAC to 240 VAC/50 Hz or 60 Hz + 3 Hz/1.8 A (Max.)

voltage/frequency/current

<0.5 W

Power consumption (standby/sleep mode)

Dimensions (with stand)

Height (compressed~extended)

402.6 mm ~ 547.1 mm (15.85 inches ~ 21.54 inches)

Width

626.4 mm (24.66 inches)

Depth

200.3 mm (7.89 inches)

Weight

Weight (panel only)

5.98 kg (13.18 lb)

Weight (with stand)

8.40 kg (18.52 lb)

Shipping weight

11.55 kg (25.46 lb)

Standard service plan

3 Years Advanced Exchange Service⁵ & Limited Hardware Warranty⁷,
Premium Panel Exchange⁴

Environmental compliance

RoHS Compliant

What's in the box?

Components

- Monitor with stand

Cables

- 1 x mDP - DP cable
- 1 x HDMI cable
- USB 3.0 upstream cable
- Power cable

Documentation

- Quick Setup Guide
- Safety and regulatory information
- Factory Calibration Report

Adjustability and connectivity

DELL ULTRASHARP 27 4K HDR MONITOR – UP2718Q

Easily adjust the panel to your preferred viewing position.



Connectivity



* Source: IDC Worldwide Quarterly PC Monitor Tracker, Q2 2019.

1 HDR standards as defined by UHD Alliance (<http://www.uhdalliance.org>), as of May 2017.

2 Dell's software development kit enables you to customize Dell UltraSharp Monitors to your preferred in-house custom system, allowing you to easily manage color space and control video layout.

3 Requires Dell UltraSharp Color Calibration Solution software, available on www.Dell.com/support. The X-Rite i1Display Pro colorimeter is available in selected countries for purchase from Dell. Contact a Dell representative to find out if it is available in your country. i1Display Pro is also available from X-Rite's North American and Pantone online stores, and X-Rite's worldwide network of resellers.

4 The Dell Premium Panel Exchange allows a free monitor replacement during the Limited Hardware Warranty period even if only one bright pixel is found.

5 Advanced Exchange Service: Replacement part/unit dispatched, if needed, following completion of phone/online diagnosis. Fee charged for failure to return defective unit. Availability varies. Other conditions apply.

6 Availability varies, please visit www.dell.com/support for details. In some countries, hours for in-region support may vary. Support after local business hours may be provided in a language other than the local language.

7 For a copy of the Limited Hardware Warranty, write Dell USA LP, Attn: Warranties, One Dell Way, Round Rock, TX 78682 or see [Dell.com/warranty](http://www.Dell.com/warranty).

8 The audio line-out port does not support headphones.