

## AC/USB Charging Clip for Display Mounts

MODEL NUMBER: **DMACUSB**



### Description

Ideal for office, hospitality, healthcare, education and any other environments where AC power and USB charging is crucial, the DMACUSB AC/USB Charging Clip attaches to your display mount pole for instant access to clutter-free device charging. The compact all-in-one design fits most display mount poles up to 1.5 inches in diameter for ergonomically friendly power. It features two integrated USB ports (3.4 total amps) for charging your cell phone, tablet and other mobile devices. It also features two NEMA 5-15R outlets for plugging in a laptop docking station and other computer peripherals. No longer will you have to crawl under or reach behind your desk just to plug something in. The removable charge adapter snaps into a holder, which is clamped securely to your display mount pole. Great for traveling, the charge adapter easily unsnaps for providing power on the go. The six-foot power cord with NEMA 5-15P plug reaches nearby wall outlets.

### Features

#### Above-Desk AC and USB Power Solution for Your Home or Office Workstation

- Attaches to monitor's display mount pole with included clamp
- Dual integrated USB-A ports with 3.4A total for charging mobile devices
- Dual integrated NEMA 5-15R outlets for connecting AC-powered peripherals
- Fits most display mount poles up to 1.5 in. diameter
- Snap-out design allows you to take removable charger anywhere
- 6 ft. power cord with NEMA 5-15P plug reaches nearby wall outlet

### Highlights

- 2 USB ports with 3.4A total for charging mobile devices
- 2 NEMA 5-15R outlets for connecting peripherals
- Fits most display mount poles up to 1.5 in. diameter
- Snap-out design allows you to take charger anywhere
- 6 ft. power cord with NEMA 5-15P plug reaches nearby wall outlet

### Package Includes

- AC/USB charge adapter
- Adapter holder
- Thumbscrew w/nut
- Clamp
- Rubber pad
- AC power cord w/NEMA 5-15P plug, 6 ft.
- Owner's manual

## Specifications

OVERVIEW	
Accessories Type	Charging Clip
OUTPUT	
Charging Ports / Amps	(2) 3.4A



Output Receptacles	(2) 5-15R
Circuit Breaker (amps)	8
Right-Angle Outlets	No
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Connection Type	NEMA 5-15P input plug
Input Plug Features	120V, 8A
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
Voltage Compatibility (VAC)	120
Right-Angle Plug	No
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Unit Dimensions (hwd / in.)	3.9 x 1.3 x 4.04
Unit Dimensions (hwd / cm)	9.9 x 3.3 x 10.3
Unit Weight (lbs.)	1
Unit Weight (kg)	0.45
Material of Construction	Plastic
Housing Color	Black
Receptacle Color	Black
<b>CERTIFICATIONS</b>	
UL1363 (Power Tap)	UL1363
Approvals	RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty; Lifetime limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>