



# HP DesignJet T520 36-in Printer

**The most affordable 36-inch HP DesignJet printer<sup>1</sup> for small businesses**



## OFFICE-READY—Fits the way you work

- Present your professional best—this compact, space-saving printer delivers consistent, outstanding results.
- Produce a range of applications, including architectural designs, maps, photos, and presentations.
- Achieve accurate lines, sharp details up to 2400 dpi from the first print with a long-life printhead.
- Save time and money—Original HP inks deliver accurate, quality prints the first time, every time.

## EASY—Convenient printing designed for sharing

- Two printers in one—print using the built-in A3/B+ tray and up to A0/E using the front-loading media roll.
- The intuitive, full-color, 4.3-inch (109-mm) touchscreen simplifies navigation and printing.
- Easily setup your printer and connect everyone in your studio, with built-in wireless connectivity.<sup>1</sup>

## MOBILE—Easily print from smartphone or tablet<sup>1</sup>

- Print straight from your Apple® or Android™<sup>2</sup> smartphone/tablet wherever you are with HP Mobile Printing.<sup>1</sup>
- If you're on-the-go, attach your document to an email and send it directly to your printer via ePrint.<sup>1</sup>
- Use the HP AiO Printer Remote<sup>3</sup> to access additional print features when printing from your mobile device.
- No LAN needed—move this printer any time, any place your Wi-Fi signal can reach with wireless connectivity.<sup>1</sup>

**For more information, please visit  
[hp.com/go/designjetT520](http://hp.com/go/designjetT520)**

<sup>1</sup> Local printing requires mobile device and printer to be on the same network (usually Wi-Fi access points bridge wireless to wired connections). Wireless performance is dependent on physical environment and distance from access point. Wireless operations are compatible with 2.4 GHz operations only. Remote printing requires an Internet connection to an HP web-connected printer. Wireless broadband use requires separately purchased service contract for mobile devices. Check with service provider for coverage and availability in your area. See <http://www.hp.com/go/designjetmobility> for more details.

<sup>2</sup> The HP Print Service Plugin app is available for Android™ mobile devices running Android™ v.4.4 or later. The app is free from Google Play.

<sup>3</sup> The HP All-in-One Printer Remote mobile app is available for Apple® iPad, iPhone, and iPod Touch running iOS v7.0 or later and for Android™ mobile devices running Android™ v4.4 or later. The HP All-in-One Printer Remote mobile app is available for free from the Apple® App Store for Apple® mobile devices and from the Google Play Store for Android™ mobile devices.

## Technical specifications

<b>Print</b>	Line drawings <sup>4</sup>	35 sec/page on A1/D, 70 A1/D prints per hour
Color images	Fast: 25.6 m <sup>2</sup> /hr (275 ft <sup>2</sup> /hr) on coated media <sup>5</sup> Best: 2.3 m <sup>2</sup> /hr (25 ft <sup>2</sup> /hr) on glossy media <sup>6</sup>	
Print resolution	Up to 2400 x 1200 optimized dpi	
Margins (top x bottom x left x right)	Roll: 5 x 5 x 5 x 5 mm (0.2 x 0.2 x 0.2 x 0.2 in) Sheet: 5 x 17 x 5 x 5 mm (0.2 x 0.67 x 0.2 x 0.2 in)	
Technology	HP Thermal Inkjet	
Ink types	Dye-based (C, M, Y); pigment-based (K)	
Ink drop	5.5 pl (C, M, Y); 12 pl (K)	
Printheads	1 (C, M, Y, K)	
Line accuracy	+/- 0.1% <sup>7</sup>	
Minimum line width	0.02 mm (0.0008 in) (HP-GL/2 addressable)	
Guaranteed minimum line width	0.07 mm (0.0028 in) (ISO/IEC 13660:2001(E)) <sup>8</sup>	
<b>Media</b>		
Handling	Sheet feed, roll feed, input tray, media bin, automatic cutter	
Weight	60 to 280 g/m <sup>2</sup> (roll/manual feed); 60 to 220 g/m <sup>2</sup> (input tray)	
Size	36-in printer: Rolls: 279 to 914 mm (11 to 36 in) Sheets: 210 x 279 to 914 x 1897 mm (8.3 x 11 to 36 x 74.7 in) Standard sheets: A4, A3, A2, A1, A0 (A, B, C, D, E)	
Thickness	Up to 11.8 mil	
<b>Memory</b>	1GB	
<b>Connectivity</b>	Interfaces (standard)	Fast Ethernet (100Base-T), Hi-Speed USB 2.0 certified, Wi-Fi
	Print languages (standard)	HP-GL/2, HP-RTL, HP PCL 3 GUI, JPEG, CALS G4
	Printing paths	Printer driver, HP DesignJet Print & Share, HP Instant Printing, Apple AirPrint
	Drivers (included)	HP-GL/2, HP-RTL drivers for Windows (optimized for AutoCAD 2000 and higher); HP PCL 3 GUI driver for Mac OS X; HP PCL 3 for Windows
<b>Dimensions (w x d x h)</b>	Printer	36-in printer: 1292 x 530 x 932 mm (50.9 x 20.9 x 36.7 in)
	Shipping	36-in printer: 1423 x 577 x 626 mm (56 x 22.7 x 24.6 in)
<b>Weight</b>	Printer	36-in printer: 39.2 kg (86.4 lb)
	Shipping	36-in printer: 62 kg (136.7 lb)
<b>What's in the box</b>	HP DesignJet T520 Printer, printhead, ink cartridges <sup>9</sup> , printer stand, quick, reference guide, setup poster, startup software, power cord	
<b>Environmental ranges</b>	Operating temperature: 5 to 40°C (41 to 104°F) Storage temperature: -25 to 55°C (-13 to 131°F) Operating humidity: 20 to 80% RH	
<b>Acoustic</b>	Sound pressure: 48 dB(A) (active); < 16 dB(A) (standby) Sound power: 6.5 B(A) (active); < 3.4 B(A) (standby)	
<b>Power consumption</b>	< 35 watts (printing), < 0.3 watts (standby) Input voltage (auto ranging) 100 to 240 VAC (+/- 10%), 50/60 Hz (+/- 3 Hz), 1200 mA max	
<b>Certification</b>	Safety	USA and Canada (CSA certified); EU (LVD and EN 60950-1 compliant); Russia (EAC); Singapore (PSB); China (CCC); Mexico (NYCE)
	Electromagnetic	Compliant with Class B requirements, including: USA (FCC rules), Canada (ICES), EU (EMC/R&TTE Directives), Australia (ACMA), New Zealand (RSM), China (CCC), Japan (VCCI); Certified as Class A product: Korea (KCC)
	Environmental	ENERGY STAR, WEEE, EU RoHS, REACH, EuP, EPEAT Bronze
<b>Warranty</b>	One-year limited hardware warranty	

## Ordering information

<b>Product</b>	CQ893B	HP DesignJet T520 36-in Printer
<b>Accessories</b>	B3Q37A	HP DesignJet T520 36-in Spindle
	B3Q36A	HP DesignJet T120/T520 24-in Spindle
<b>Original HP printhead</b>	C1Q10A	HP 711 DesignJet Printhead Replacement Kit
<b>Original HP ink cartridges</b>	CZ129A	HP 711 38-ml Black Ink Cartridge
	CZ130A	HP 711 29-ml Cyan Ink Cartridge
	CZ131A	HP 711 29-ml Magenta Ink Cartridge
	CZ132A	HP 711 29-ml Yellow Ink Cartridge
	CZ133A	HP 711 80-ml Black Ink Cartridge
	CZ134A	HP 711 3-pack 29-ml Cyan Ink Cartridges
	CZ135A	HP 711 3-pack 29-ml Magenta Ink Cartridges
	CZ136A	HP 711 3-pack 29-ml Yellow Ink Cartridges
<b>Original HP large format printing materials</b>	C6036A	HP Bright White Inkjet Paper (FSC® certified) <sup>10</sup>  914 mm x 45.7 m (36 in x 150 ft)
	C6020B	HP Coated Paper  914 mm x 45.7 m (36 in x 150 ft)
	C6030C	HP Heavyweight Coated Paper  914 mm x 30.5 m (36 in x 100 ft)
	C3875A	HP Clear Film  914 mm x 22.9 m (36 in x 75 ft)
<b>Service and support</b>	24-in	36-inc
	U1W23E	HP 3 year Next Business Day Onsite Support
	U1V85E	HP 3 year 4-hour response, 13x5 Onsite Support <sup>12</sup>
	U1V90PE	HP 1 year Post Warranty, Next Business Day Onsite Support
	U1V93PE	HP 1 year Post Warranty, 4-hour response, 13x5 Onsite Support <sup>12</sup>

**HP DesignJet Support Services** offer solutions for business critical environments — installation, extended support and maintenance, as well as variety of value added services.  
For more information, please visit [hp.com/go/designjetsupport](http://hp.com/go/designjetsupport).

Use **Original HP inks**, printheads and large format printing materials to experience consistent high quality and reliable performance that enable less downtime. These critical components are designed and engineered together as an optimized printing system to provide precise line accuracy as well as dark blacks.

For more information, visit [hp.com/go/OriginalHPinks](http://hp.com/go/OriginalHPinks).

For the entire **HP Large Format Printing Materials** portfolio, please visit [HPLFMedia.com](http://HPLFMedia.com).

<sup>4</sup> Mechanical printing time. Printed in Fast mode on plain paper with Original HP inks.

<sup>5</sup> Mechanical printing time with Original HP inks. Measured on a 36-in printer.

<sup>6</sup> Mechanical printing time with Original HP inks. Measured on a 24-in printer.

<sup>7</sup> +/-0.1% of the specified vector length or +/-0.2 mm (whichever greater) at 23°C (73°F), 50-60% relative humidity, on A0/E printing material in Best or Normal mode with HP Heavyweight Coated roll feed and Original HP inks.

<sup>8</sup> Measured on HP Matte Film.

<sup>9</sup> Standard ink cartridges included with 36-in printer.

<sup>10</sup> FSC® trademark license code FSC®-C017543, see [fsc.org](http://fsc.org). PEFC™ trademark license code PEFC™/29-31-198, see [pefc.org](http://pefc.org). Not all FSC®- or PEFC™-certified products are available in all regions.

<sup>11</sup> Can be recycled through commonly available recycling programs.

<sup>12</sup> Not available in North America, and Latin America.



For more information, please visit  
[hp.com/go/designjetT520](http://hp.com/go/designjetT520)

© Copyright 2016-2017 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

ENERGY STAR and the ENERGY STAR mark are registered trademarks owned by the U.S. Environmental Protection Agency.

Adobe, PostScript, and Adobe PostScript 3 are trademarks of Adobe Systems Incorporated. Windows is a U.S. registered trademark of Microsoft Corporation. Mac and the Mac logo are trademarks of Apple Computer, Inc., registered in the U.S. and other countries.

4AA4-1675EEP, July 2017, Rev.1

