


12U 19" Wall Mount Network Rack - 12" Deep 2 Post Open Frame Server Room Rack for Data/AV/IT/ Communication/Computer Equipment/Patch Panel w/Cage Nuts & Screws 200lb Capacity

Product ID: RK12WALLO



This open-frame wall-mount server rack provides 12U of storage, allowing you to save space and stay organized. The equipment rack can hold up to 198 lb. (90 kg).

Easy, hassle-free installation

The network rack is 12 in. (30.4 cm) deep, so it's perfect for smaller spaces. It's easy to assemble and features mounting holes that are spaced 16 in. apart, making it suitable for mounting on almost any wall, based on common wall-frame stud spacing. The wall-mount rack comes in a flat-pack which makes it easy to transport and reduces shipping costs.

Free up space

You can mount the open-frame rack where space is limited, such as on a server room wall, office, or above a doorway, to expand your workspace and ensure your equipment is easy to access.

Keep your equipment cool and accessible

By having an open frame the server rack provides passive cooling to equipment. Additionally, the open frame provides easy access and configurability to your equipment, allowing you to maximize productivity.

The RK12WALLO is backed by a StarTech.com 5-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Perfect for installing network switches out of the way and high up on a wall in a branch office, warehouse, or superstore location
- Mount audio/video broadcast or distribution components
- Ideal for small and medium businesses requiring small rack solutions dispersed throughout the organization

Features

- **STURDY & CONVENIENT:** 12U 19" Open Frame wall mount network rack with 12" mounting depth is EIA/ECA-310 compatible & supports like patch panels, shelves and unmanaged switches
- **HEAVY DUTY:** This heavy duty 2 post open frame rack supports unobstructed airflow & is easy to install with a durable design made from SPCC cold-rolled steel with support for up to 200lbs of equipment
- **EASY ASSEMBLY:** The rack ships flat packed with ISTA-6 certified packaging to ensure complete and undamaged delivery and also features comprehensive assembly instructions
- **ACCESSORIES INCLUDED:** The wall mount server room/computer/communication/AV/IT equipment rack includes a complete set of 60 screws and cage nuts to securely mount all of your equipment in the rack
- **LIFETIME WARRANTY:** StarTech.com offers 24 hour technical support and has been the choice of IT professionals for 30 years, conducting thorough compatibility and performance testing on all our products

Hardware	Warranty	5 Years
	Frame Type	Open Frame
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	G-Shape
	Rack Type	2-Post
	Special Features	Easy Assembly
		U-Markings
	Wall-Mountable	
	U Height	12U
	Wallmountable	Yes
Performance	Weight Capacity	198.9 lb [90 kg]
Physical Characteristics	Color	Black
	Construction Material	Steel
Product Measurements	Maximum Mounting Depth	12 in [30.5 cm]
	Product Height	25.2 in [64.1 cm]
	Product Length	12 in [30.5 cm]
	Product Width	19.8 in [50.4 cm]
	Weight of Product	19.1 lb [8.7 kg]
Packaging Information	Flat Pack (Assembly Required)	Yes
	Package Height	5.1 in [13 cm]
	Package Length	26.4 in [67 cm]
	Package Width	20.9 in [53 cm]
	Shipping (Package) Weight	24.3 lb [11 kg]
What's in the Box	Included in Package	48 - M6 Screws
		48 - M6 Cage Nuts
		48 - Washers
		16 - Assembly Screws
		2 - Vertical Rails
		2 - Horizontal Brackets

Product appearance and specifications are subject to change without notice.