

P300 NEO

PICO PROJECTOR



TINY | BRIGHT | MOBILE

1280X720 HD NATIVE RESOLUTION

420 LUMENS | 30K HOUR LEDS | 2.5 HOUR BATTERY

HD Entertainment Anytime, Anywhere

Incorporating the latest in LED technology along with a 1280x720p imager, the P300 Neo produces a vivid high definition picture anytime, anywhere. Powered by a 30,000 hour LED light source and a 150 minute lithium ion battery, the P300 Neo can deliver up to 120" images in dark areas* with 420 lumens and offers best-in-class resolution for both its size and price.



Photos



Music



Text



Videos



Onboard Media Player



30,000 Hour LED



150 Minute Battery



120" Screen Size



Digital Keystone



PROJECTION SYSTEM

Max Resolution: 1920x1080 (1080p)

Native Resolution: 1280x720 (720p)

Max Brightness (DC): 420 Lumens

Contrast Ratio: 1000:1

Projection Lens: Manual Focus

Projection Image Size: 10"-120"

Lamp: Triple RGB LEDs with Vibrant Color Technology - Life 30,000hrs

GENERAL SPECIFICATIONS

Battery Runtime: 150 Minutes (Eco Mode)

Audio Output: 1W Speaker

3.5mm Headphone Output

Color: Black / White

File Playback: MicroSD & USB Host reader

Menu Language: English, Spanish, French, Chinese (Traditional/Simplified), Dutch, Korean, & Japanese

Aspect Ratio Control: 16:9

Dimensions: 5.9" x 3.5" x 1.2"

Weight: 0.84 LBS

Power Consumption: 24 Watts

Supported Formats: MP3 / WMA / OGG / WAV / AVI / BMP / JPG / GIF / TXT

Conformances: CE, FCC Class A



INPUTS / OUTPUTS

Video In: HDMI, Composite A/V (3.5mm Jack), mini-VGA

Audio Out: 3.5mm Stereo Headphone Jack

USB: Full Sized USB 2.0

INCLUDED ACCESSORIES

- ✓ User Manual
- ✓ Tripod
- ✓ Composite AV Cable
- ✓ Wall Charger
- ✓ Remote Control
- ✓ VGA Adapter Cable

ONBOARD MEDIA PLAYER

Processor: ARM Cortex 1.3 ghz

Operating System: Linux Based

THROW RATIO

Throw Ratio: 1.2

Projection Offset: 100%



Digital Video Input



TF Card/USB



VGA Input



Composite A/V



3.5mm Audio Jack



P300 NEO
PICO PROJECTOR

www.aaxatech.com

aaxa
TECHNOLOGIES