



MondoHub II

Adds 28 USB Ports to Any Computer – 24 USB 2.0 & Four USB 3.0 Ports, AC Power, Black

Part No.: **163606**

The Manhattan MondoHub II features a high-capacity, four-amp power adapter and has enough ports to manage a growing collection of USB-enabled devices. Unlike some other large-capacity USB hubs available on the market, the MondoHub II features four SuperSpeed USB 3.0 ports and can recharge devices or transfer data at lightning-fast speeds.

The compact and durable case features the power and hub-to-PC ports on a side panel to help better organize connections and minimize cable clutter. This high-quality USB hub also features automatic overcurrent protection for each port and hot-swapping plug-and-play connection. With a power switch for each port, the MondoHub II gives users complete control over which devices are using power or valuable system resources.

Features:

- Provides 28 Hi-Speed USB ports for additional peripherals
- 24 USB 2.0 ports
- Four USB 3.0 ports
- Replaces less-capable hubs with compact multiport design and high-capacity 4-amp power adapter
- Conveniently recharges mobile devices and connects flash drives, receivers, card readers and more
- Switch each port on and off individually
- Use the Manhattan part 354196, USB power cable, if included power adapter is not needed
- Overcurrent protection; hot-swappable
- Compatible with all USB-equipped computers
- Plug and play; Windows and Mac compatible
- Three-Year Warranty

Specifications:

Standards and Certifications

- USB 3.0
- FCC
- CE
- RoHS

Ports

- Transfer speeds: 1.5 / 12 / 480 Mbps / 5 Gbps
- Upstream plug: Standard-A
- 24 downstream ports: USB 2.0 Standard-A
- Four downstream ports (1, 2, 15 and 16): USB 3.0 Standard-A
- Ports 13, 14, 27 and 28 charge Apple devices
- 5 VDC port
- Up to 500 mA power, all ports

Physical

- Dimensions: 23 (h) x 229 (w) x 112 (d) mm [0.9 (h) x 9 (w) x 4.4 (d) in.]
- Weight: 354 g (12.5 oz.)
- Incorporated USB 3.0 cable: 75 cm (30 in.)
- Housing: plastic
- LED power indicator

Power Adapter

- cUL, FCC
- Input: 100 - 240 V, 50/60 Hz; 1.6 A, maximum
- Output: 5 V / 4 A; if more power is needed, this hub will support a power adapter that provides output at up to 5 V / 5 A
- Cable: 1.2 m (6 ft.)
- DC Tip dimensions: 3.5 x 1.35mm

Environmental

- Operational temperature: 0 – 45°C (32 – 113°F)
- Storage temperature: -15 – 60°C (5 – 140°F)
- Working humidity: <85%

System Requirements

- USB-enabled PC or Mac system
- Windows 7/8.1/10 or Mac OS 10 or above
- Available USB 2.0 or USB 3.0 port

Package Contents

- MondoHub II
- Power adapter
- Instructions

