



7th Generation Intel® Core™ i7 Processor. The Intel® Open Pluggable Specification (OPS) PC is designed to turn your Avocor Interactive Display into a big-screen all-in one touch PC

- 7th generation “Kaby Lake” Intel® Core™ CPU
- 16GB DDR4 2400MHz RAM
- 4K Imagery and playback @ 60Hz
- HDMI Out - Secondary Display Connection
- Windows 10 Pro
- 2 year return to base warranty
- OPS (open pluggable specification) compliant
- Avocor Note by Nureva software included

Specification

Processor	Intel® Core™ i7-7500U Dual Core
Memory	16GB (SODIMM) DDR4 2400MHz
Storage	1 x 2.5" SATA 1 x M.2 2242 240GB SSD
Graphics	Intel® HD Graphics 620 Supports DirectX 12, OpenGL 4.4
Network	Gigabit Ethernet
Wireless	1 x M.2 2230 Wi-Fi Module
Audio	Realtek RTL662 HD Audio IC
Front input/output ports	2 x USB 3.0 Type-A 2 x USB 2.0 Type-A 1 x RJ45 10/100/1000M 1 x HDMI 1.4 out, max 4K/24Hz 1 x 3.5mm line out 1 x 3.5mm mic in 2 x WIFI/BT antennae 1 x IR receiver 1 x Power button 1 x Power LED 1 x HDD/SSD LED
JAE 80-pin connector	1 x HDMI 2.0 out, 4K/60Hz, 3 x USB 2.0/3.0 TTL

TPM	Trusted Platform Module 2.0 firmware
Supported OS	Windows 10 Pro
Dimensions	180mm x 120mm x 30mm
Net weight	900g
Material	Metal
Power Input	12-19V DC IN
Operating Temperature	-5°C to 45°C
Storage Temperature	-20° to 70°
Relative humidity	10% to 95% (non-condensing)
EMC	CE/FCC Class B, CCC
Safety	CE/FCC LVD, CCC

