

QCW3MP

| | |
|-----------------------------|--------------------|
| Camera Type | Wi-Fi Smart camera |
| Camera Technology | Wi-Fi |
| Image Sensor Size | 1/3" 3 Megapixel |
| Image Sensor Type | CMOS |
| Megapixels (digital) | 3 MP |
| Effective Pixels | 2304 x 1296 |
| Lens Size | 2.3 mm fixed lens |
| Angle of View | 120° |
| IR Cut Filter | Yes |
| Max. User Access | 20 users |
| Storage | SD Card Max.128 GB |



NIGHT VISION

| | |
|----------------------|--|
| Night Vision Range | Up to 33 ft |
| Infrared Wavelength | 850nm |
| Min Lux Illumination | 0.9 Lux /F2.2 (color), 0 Lux /F2.2 (IR on) |

ADDITIONAL IMAGE FEATURES

| | |
|------------------------|---------------|
| Auto Iris | No |
| On Screen Display | No |
| Backlight Compensation | Yes |
| Electronic Shutter | NA |
| Gain Control | Auto / Manual |
| Wide Dynamic Range | DWDR |
| Noise Reduction | 3D |

REMOTE MONITORING

| | |
|---------------------------|----------------------------|
| Use as Standalone | Yes |
| Compatible Mobile Devices | iPhone, iPad, Android |
| Compatible Systems | Q-See IP NVR(s)/ ONVIF CGI |

RESOLUTION AND FRAME RATE

| | |
|---------------------|--------|
| 3MP (2304 x 1296) | 20 FPS |
| 1080p (1920 x 1080) | 30 FPS |
| 720p (1280 x 720) | 30 FPS |
| VGA (640 x 480) | 30 FPS |
| QVGA (320x 240) | 30 FPS |

PTZ

| | |
|----------------------------|----------------|
| Horizontal Rotation | Not applicable |
| Vertical Tilt | Not applicable |
| Preset and Cruise Patterns | Not applicable |

AUDIO

| | |
|-------------------|----------------------|
| Audio Compression | G.711A; G.711Mu; AAC |
| Audio Microphone | Yes |
| Speaker | Yes |

CONNECTIVITY

| | |
|-------------------|---------------------------|
| Connector Types | NA |
| Other Connections | 2.1 mm Power |
| Wireless | Wi-Fi 802.11 b/g/n 2.4Ghz |
| Wireless Range | 50m Line Of Sight |

POWER

| | |
|-------------------|--------|
| Power Supply | 5V 1A |
| Power Consumption | < 4.7W |

PHYSICAL ATTRIBUTES

| | |
|-----------------------|-----------------------|
| Weatherproof | No |
| IP Rating | NA |
| Body Construction | Plastic |
| Mounting Hardware | Screws/Magnetic |
| Weight | 4.8 oz |
| Dimensions | 2.54" x 2.19" x 4.21" |
| Operating Temperature | 14°F to 113° F |