

# Cat6 Straight-Through Modular Compact In-Line Coupler (RJ45 F/F), White, TAA

# MODEL NUMBER: N234-001-WH





Connects two Cat6 cables to create one longer cable. Provides feed-through patching for easy installation. Ideal for premise wiring, telecommunications, data networking and Ethernet connections.

## Description

Strengthen your high-speed network with Tripp Lite's N234-001-WH Cat6 Straight-Through Modular Compact In-Line Coupler. It connects two Cat6 patch cords to create one longer cable, and its compact inline design is recommended for convenient feed-through patching. Built for ultra-fast performance, this is an ideal coupler when setting up premise wiring, voice/data networking, telecommunications and Ethernet connections.

Compatible with all Cat6 cables, the N234-001-WH features straight-through wiring and 50-µinch goldplated contacts designed to resist corrosion. The durable, high-impact polycarbonate housing resists scratching and is colored white to blend in with any color scheme. This coupler is UL-listed and meets all requirements for EIA/TIA Cat6 compliance. It's also backward compatible with Cat5e and Cat5 LANs.

## Features

#### Strengthens Your High-Speed Network

- Ideal for premise wiring, voice/data networking, telecommunications and Ethernet connections
- Connects 2 Cat6 patch cables for a longer cable run
- Compact in-line design recommended for convenient feed-through patching
- Compatible with all Cat6 cables
- Backward compatible with Cat5e and Cat5 LANs

#### Superior Construction for Superior Performance

- Features straight-through wiring
- 50-µinch gold-plated contacts resist corrosion and improve conduction

# Highlights

- 50-µinch gold-plated contacts on RJ45 jacks
- Heavy-duty polycarbonate housing
- · Compact, clean-looking design
- Compatible with all Cat6 cables
- Backward compatible with Cat5e and Cat5 LANs

#### **Package Includes**

 N234-001-WH Cat6 Straight-Through Modular Compact In-Line Coupler (RJ45 F/F), White



- Durable, scratch-resistant polycarbonate housing
- White coloring blends into any color scheme
- UL-listed
- Meets all EIA/TIA Cat6 requirements

#### **TAA-Compliant**

• Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

# **Specifications**

OVERVIEW	
UPC Code	037332203410
Technology	Cat5/5e; Cat6
PHYSICAL	
Color	White
Cable Length (ft.)	0
Cable Length (m)	0
Shipping Dimensions (hwd / cm)	1.27 x 10.16 x 13.46
Shipping Dimensions (hwd / in.)	0.50 x 4.00 x 5.30
Shipping Weight (kg)	0.01
Shipping Weight (lbs.)	0.01
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	-40 to 154 F (-40 to 68 C)
Relative Humidity	10% to 90% RH, Non-condensing
CONNECTIONS	
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	RJ45 (FEMALE)
РоЕ Туре	Type 3 PoE++/UPoE (60W, IEEE 802.3bt)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.



Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <u>https://www.tripplite.com/products/product-certification-agencies</u>