

Expression® Photo HD XP-15000 Wide-format Printer

Wireless | Wide-format | Print | ^{ULTRA}HD Photo | Ethernet



Wide-format Printer
Photo

Wide-format printer with 6-color Ultra HD inks for stunning photos.

Professional Ultra HD photo quality — get brilliant borderless prints up to 13" x 19"

Individual 6-color Claria® Photo HD Ink — includes Red and Gray inks for an ultra wide color gamut and enhanced black-and-white prints

Professional projects made easy — features a 50-sheet rear tray for specialty media, including cardstock¹; accommodates a variety of paper finishes and borderless sizes from 4" x 6" to 13" x 19"

Ultra compact wide-format A3+ printer — 30 percent smaller than its predecessor²; easily fits on your desktop

Convenient printing features — supports auto 2-sided document printing, with a 200-sheet front tray

Fast speeds — prints documents at 9.2 ISO ppm (black) and 9.0 ISO ppm (color)[†] and 4" x 6" borderless photos in as fast as 27 seconds³

Ultimate wireless and wired connectivity — easily print from iPad®, iPhone® and Android™ tablets and smartphones⁴; also offers Ethernet networking

Simple setup and navigation — easy-to-use 2.4" color LCD

Hassle-free — features an auto open/close output tray and direct CD/DVD printing

PC-free photo printing — includes a USB port for quick printing from flash drives and devices

Designed for use exclusively with Epson® cartridges.*



312/312XL (CMYK)



314XL (R/GY)

Print

Printing Technology 6-color (C, M, Y, K, GY, R), drop-on-demand MicroPiezo[®] inkjet technology
Printer Language Epson ESC/P[®] Raster, ESC/P-R
Maximum Print Resolution 5760 x 1440 optimized dpi
Print Speed[†] 9.2 ISO ppm (black), 9.0 ISO ppm (color)
Auto 2-sided Print Speed[†] 4.7 ISO ppm (black), 4.7 ISO ppm (color)
Max. Photo Speed[‡] 4" x 6" borderless photo in as fast as 27 sec (Draft Mode)
Min. Ink Droplet Size Variable droplet as small as 1.5 picoliters

Mobile Printing

Epson Connect™ Solutions⁴ Epson E-mail Print, Epson Remote Print, Epson iPrint™ App (iOS[®], Android), Creative Print App (iOS, Android)
Other Apple[®] AirPrint[®], Google Cloud Print™, Android printing, Fire OS™ printing, Mopria[®] Print Service

Connectivity

Standard Connectivity

Hi-Speed USB
 USB Host
 Wireless 802.11 b/g/n⁵
 Wi-Fi Direct^{6,5}
 Ethernet 10/100

Operating Systems Windows[®] 10 8/8.1/Windows 7 (32-bit, 64-bit), Windows Vista[®] (32-bit, 64-bit)
 Mac[®] OS X[®] 10.6.8 – macOS[®] 10.12.x⁶

Paper Handling

Max. Paper Size 13" x 44"
Paper Sizes 4" x 6", 5" x 7", 8" x 10", A4 (8.3" x 11.7"), letter (8.5" x 11"), legal (8.5" x 14"), 11" x 14", 12" x 12", B (11" x 17"), A3 (11.7" x 16.5") and Super B (13" x 19"), user definable (2.2" – 44" in length)
Borderless Photo Sizes 4" x 6", 5" x 7", 8" x 10", A4 (8.3" x 11.7"), letter (8.5" x 11"), 11" x 14", B (11" x 17"), 12" x 12" and Super B (13" x 19")
Paper Types Plain paper, Epson Bright White Paper, Brochure & Flyer Paper Matte Double-sided, Ultra Premium Presentation Paper Matte, Premium Presentation Paper Matte, Premium Presentation Paper Matte Double-sided, Presentation Paper Matte, Ultra Premium Photo Paper Luster, Ultra Premium Photo Paper Glossy, Premium Photo Paper Semi-gloss, Premium Photo Paper Glossy, Photo Paper Glossy, Photo Quality Adhesive Sheets, Iron-on Cool Peel Transfer paper
Envelope Types No. 10
Input Paper Capacity 50 sheets plain paper (legal), 200 sheets plain paper (letter), 50 sheets photo paper, 10 envelopes
Rear Feed! 50 sheets A3+ plain paper, 20 sheets Premium Photo Paper Glossy, 10 envelopes
Output Paper Capacity 100 sheets plain paper/20 sheets Premium Photo Paper Glossy

General

Display 2.4 color LCD
Temperature
 Operating: 50 ° to 95 °F (10 ° to 35 °C)
 Storage: -4 ° to 104 °F (-20 ° to 40 °C)
Relative Humidity
 Operating: 20 – 80%
 Storage: 5 – 85% (no condensation)
Sound Level
 Power: 6.2 B(A)
 Pressure: 49 dB(A)
Rated Voltage AC 100 – 120 V
Rated Frequency 50 – 60 Hz
Rated Current 0.6 Amp
Power Consumption
 Standalone Copy Printing: Approx. 21 W (ISO 24712)
 Ready: Approx. 5.7 W
 Sleep: Approx. 0.7 W
 Power Off: Approx. 0.2 W (ENERGY STAR[®] qualified)

Safety Approvals

UL60950, CSA 22.2 No. 60950
 EMI FCC Part 15 subpart B class B
 CAN/CSA-CEI/IEC CISPR 22 class B

Weight and Dimensions (W x D x H)

Printing: 18.7" x 30.9" x 16.2" (476 x 785 x 412 mm)
 Storage: 18.7" x 14.5" x 6.3" (476 x 369 x 159 mm)
 Product Weight: 18.7 lb (8.5 kg)

What's in the Box Expression Photo HD XP-15000 printer, CD-ROM for product setup, power cord, 4x Claria Photo HD 312-l ink cartridges (1x Black, 1x Cyan, 1x Magenta, 1x Yellow), 2x Claria Photo HD 314-l ink cartridges (1x Gray, 1x Red), 1 Cleaning Sheet

Software Included Epson printer driver
 Internet connection required for installation of some software

Warranty 1-year limited warranty in the U.S. and Canada

Country of Origin Indonesia

Ink

Ink Type Claria Photo HD Ink
Ink Cartridges 6 individual ink cartridges: 4x 312 ink (1x Black, 1x Cyan, 1x Magenta, 1x Yellow); 2x 314XL ink (1x Gray and 1x Red)
Replacement Ink Cartridges⁷
 312 Standard-capacity Black, Cyan, Magenta, Yellow (ISO page yields — Black: 240, Color: 360)
 312XL High-capacity Black, Cyan, Magenta, Yellow (ISO page yields — Black: 500, Color: 830)
 314XL High-capacity Red (ISO page yields — 830)
 314XL High-capacity Gray (ISO page yields — 830)
 Printer is designed to work with Epson cartridges only, not third-party cartridges or ink*.

Eco Features

Save up to 50% on paper with automatic 2-sided printing
 ENERGY STAR qualified
 RoHS compliant
 Recyclable product⁸
 Epson America, Inc. is a SmartWay[®] Transport Partner⁹

Ordering Information

Expression Photo XP-15000 C11CG43201

*This product uses only genuine Epson-brand cartridges. Other brands of ink cartridges and ink supplies are not compatible and, even if described as compatible, may not function properly.
 † Black and color print speeds are measured with letter-size paper, in accordance with ISO/IEC 24734. Actual print times will vary based on factors including on system configuration, software, and page complexity. For more information, visit www.epson.com/printspeed | 1 Specialty paper support accommodated through rear paper feed, maximum 23 mil paper thickness, manual 2-sided printing only. | 2 As compared to the Epson Artisan[®] 1430 printer dimensions. | 3 Color photo in Draft Mode on Premium Photo Paper Glossy measured from start of paper feed. Actual print times will vary based on factors including system configuration, software, and page complexity. For more information, visit www.epson.com/printspeed | 4 Most features require an Internet connection to the printer, as well as an Internet- and/or email-enabled device. For a list of Epson Connect enabled printers and compatible devices and apps, visit www.epson.com/connect | 5 Wi-Fi CERTIFIED™; level of performance subject to the range of the router being used. Wi-Fi Direct may require printer software. | 6 Some applications and/or functions may not be supported under Mac OS X. | 7 Replacement cartridge yields are based on ISO/IEC 24711 tests in Default Mode printing continuously. Replacement cartridge photo yields are significantly lower and are based on the ISO/IEC 29103 pattern with Epson's methodology. Cartridge yields vary considerably for reasons including images printed, print settings, temperature and humidity. Yields may be lower when printing infrequently or predominantly with one ink color. All ink colors are used for printing and printer maintenance, and all colors have to be installed for printing. For print quality, part of the ink from the included cartridges is used for printer startup and a variable amount of ink remains in the cartridges after the "replace cartridge" signal. For more information, visit www.epson.com/inkinfo | 8 For convenient and reasonable recycling options, visit www.epson.com/recycle | 9 SmartWay is an innovative partnership of the U.S. Environmental Protection Agency that reduces greenhouse gases and other air pollutants and improves fuel efficiency.

Better Products for a Better Future[™]
eco.epson.com



Epson America, Inc.
 3840 Kilroy Airport Way, Long Beach, CA 90806

Epson Canada Limited
 185 Renfrew Drive, Markham, Ontario L3R 6G3

www.epson.com
www.epson.ca

Contact:

Specifications and terms are subject to change without notice. EPSON, Artisan, Claria, Epson ESC/P, Expression and MicroPiezo are registered trademarks, EPSON Exceed Your Vision is a registered logomark and Better Products for a Better Future, Epson Connect and Epson iPrint are trademarks of Seiko Epson Corporation. AirPrint, Apple, iPad, iPhone, Mac, macOS and OS X are trademarks of Apple Inc., registered in the U.S. and other countries. Android and Google Cloud Print are trademarks of Google Inc. Windows and Windows Vista are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. Wi-Fi Direct[®] is a registered trademark and Wi-Fi CERTIFIED™ is a trademark of Wi-Fi Alliance[®]. SmartWay is a registered trademark of the U.S. Environmental Protection Agency. All other product and brand names are trademarks and/or registered trademarks of their respective companies. Epson disclaims any and all rights in these marks. Copyright 2017 Epson America, Inc. Inc. Com-SS-Oct-13 CPD-54342 9/17