

## USB-C to DVI Adapter with USB-A Hub, Thunderbolt 3—1080p, PD Charging, Black, 6 in.

MODEL NUMBER: **U444-06N-DUB-C**



### Features

### Highlights

- Transmits video signals from sources supporting USB DisplayPort Alt Mode
- Delivers HD picture quality at resolutions up to 1920 x 1080 (1080p) @ 60 Hz
- BC 1.2-compliant USB-A port provides up to 1.5A of fast-charging power
- Powers and charges PD Charging-compliant devices, such as MacBooks and Chromebooks
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Easy installation with plug-and-play operation—no software required

### Applications

- Play 1080p video from your laptop or PC on a DVI display
- Charge your notebook or laptop by connecting its wall charger to the USB-C PD Charging port
- Transfer files to and from a USB thumb drive or external hard drive
- Attach a USB headset/microphone for recording your podcast
- Write a report using a USB keyboard with your tablet or Android smartphone

### System Requirements

- Source device with USB-C or

Thunderbolt 3 port that supports  
USB DisplayPort Alternate  
Mode

- Display device with DVI input  
(DVI port)

#### Package Includes

- U444-06N-DUB-C USB-C to  
DVI Adapter with USB-A Hub,  
Thunderbolt 3—1080p, PD  
Charging, Black, 6 in.
- Owner's manual

## Specifications

MODEL TEXT	
What Does This Product Do?	USB Type-C to DVI adapter adds DVI, USB-A and USB-C PD charging ports to your tablet, laptop, smartphone or PC.
OVERVIEW	
Over Current Protection	
INPUT	
Cable Length (ft.)	
Cable Length (m)	
Cable Length (in.)	
Built-In Cable Length (ft.)	
Built-In Cable Length (m)	
Built-In Cable Length (in.)	
Built-In Cable Length (cm)	
External Power Supply Input Specs (V / Hz / A)	
External Power Supply Output Specs (V / A)	
External Power Supply Cord Length (ft.)	
External Power Supply Cord Length (m.)	
Bus Powered	Yes

Cable Length (cm)	
Product Length (in.)	6.00
Product Length (cm.)	
Product Length (ft.)	
Product Length (m.)	
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	0.91 x 5.5 x 3.9
Shipping Weight (lbs.)	0.10
Unit Packaging Type	Box
Unit Dimensions (hwd / in.)	0.57 x 3.1 x 1.6
Unit Dimensions (hwd / cm)	
Unit Weight (lbs.)	0.08
Unit Weight (kg)	0.04
Material of Construction	PVC and ABS
Color	Black
Transmitter Unit Dimensions (hwd / in.)	
Transmitter Unit Dimensions (hwd / cm.)	
Receiver Unit Dimensions (hwd / in.)	
Receiver Unit Dimensions (hwd / cm.)	
Transmitter Unit Weight (lbs.)	
Transmitter Unit Weight (kg)	
Receiver Unit Weight (lbs.)	
Receiver Unit Weight (kg)	
Cable Jacket Rating	VW-1
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
Relative Humidity	
Operating Elevation (ft.)	
Storage Elevation (ft.)	

BTUs	4.1 BTU/Hr
Power Consumption (Watts)	1.2
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	5V 0.9A (4.5W) Output (USB-A), Up to 20V 3A (60W) Input (USB-C)
<b>COMMUNICATIONS</b>	
Signal Range (ft.)	
<b>CONNECTIONS</b>	
Ports	3
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
Side B - Connector 2	USB 3.0 A (FEMALE)
Side B - Connector 3	USB C (FEMALE)
Connector Plating	Nickel
<b>PORT EXPANSION</b>	
Max Distance (Between any 2 Units)	
<b>FEATURES &amp; SPECIFICATIONS</b>	
Max Supported Video Resolution	1920 x 1080 (1080p) @60Hz
HDCP Specification	1.3
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Audio Specification	
Driver Required	No
Recommended Category Cable	
USB Power Delivery (PD) Charging Support	Yes
<b>CERTIFICATIONS</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>