



4-Port USB 3.1 Hub, 4x USB-A, Thunderbolt—Black

MODEL NUMBER: U460-004-4AB











Features

Highlights

- Supports USB 3.1 Gen 1 for fast data transfers up to 5 Gbps
- Accepts up to 4 USB peripherals, turning your laptop into a mini workstation
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- USB ports provide up to 1.5A for charging smartphones and other devices
- Easy installation with plug-andplay operation—no software required

Applications

- Transfer files to and from a USB thumb drive or external hard drive
- Connect your smartphone or other mobile device to build up a full charge
- Attach a USB headset/microphone for recording your podcast
- Write a report using a USB keyboard with your tablet or Android smartphone

System Requirements

 Tablet, laptop, Chromebook, MacBook, smartphone or PC with USB-C or Thunderbolt 3 port

Package Includes

U460-004-4AB 4-Port USB 3.1
Hub, 4x USB-A,





Thunderbolt—Black

Specifications

MODEL TEXT		
What Does This Product Do?	USB 3.1 Type-C hub adds 4 USB-A ports to your laptop, MacBook, Chromebook or other compatible device.	
OVERVIEW		
Over Current Protection		
INPUT		
Cable Length (ft.)		
Cable Length (m)		
Cable Length (in.)		
Built-In Cable Length (ft.)		
Built-In Cable Length (m)		
Built-In Cable Length (in.)		
Built-In Cable Length (cm)		
External Power Supply Input Specs (V / Hz / A)		
External Power Supply Output Specs (V / A)		
External Power Supply Cord Length (ft.)		
External Power Supply Cord Length (m.)		
Bus Powered	Yes	
Cable Length (cm)		
Product Length (in.)	12.00	
Product Length (cm.)	30	
Product Length (ft.)	1	
Product Length (m.)	0	
USER INTERFACE, ALERTS & CONTROLS		
LED Indicators	1-White for Power	
PHYSICAL		



Chinning Dimongians (build Lin)		
Shipping Dimensions (hwd / in.)		
Shipping Weight (lbs.)		
Unit Packaging Type	Box	
Unit Dimensions (hwd / in.)	0.84 x 3.8 x 1.2	
Unit Dimensions (hwd / cm)	2.14 x 9.65 x 3.05	
Unit Weight (lbs.)	0.00	
Unit Weight (kg)	0.00	
Material of Construction	PVC, Plastic	
Color	Black	
Transmitter Unit Dimensions (hwd / in.)		
Transmitter Unit Dimensions (hwd / cm.)		
Receiver Unit Dimensions (hwd / in.)		
Receiver Unit Dimensions (hwd / cm.)		
Transmitter Unit Weight (lbs.)		
Transmitter Unit Weight (kg)		
Receiver Unit Weight (lbs.)		
Receiver Unit Weight (kg)		
Cable Jacket Rating	VW-1	
ENVIRONMENTAL		
Operating Temperature Range	32 to 113 F (0 to 45 C)	
Storage Temperature Range	14 to 158 F (-10 to 70 C)	
Relative Humidity	20% to 80% RH, Non-Condensing	
Operating Elevation (ft.)		
Storage Elevation (ft.)		
BTUs	2.4 BTU/Hr	
Power Consumption (Watts)	0.7	
Operating Humidity Range		
Storage Humidity Range		
Power Provided to Connected Device(s)	Up to 5V 1.5A (7.5W) per USB Port	
COMMUNICATIONS		
Signal Range (ft.)		





CONNECTIONS		
Ports	4	
Side A - Connector 1	USB C (MALE)	
Side B - Connector 1	(4) USB 3.0 A (FEMALE)	
Connector Plating	Nickel	
PORT EXPANSION		
Max Distance (Between any 2 Units)		
FEATURES & SPECIFICATIONS		
Max Supported Video Resolution		
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)	
Audio Specification		
Driver Required	No	
Recommended Category Cable		
CERTIFICATIONS		
Certifications	Tested CE, FCC, RoHS, REACH	
WARRANTY		
Product Warranty Period (Worldwide)	3-year limited warranty	

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies