

## Keyspan Mini DisplayPort to Active VGA Adapter, Video Converter (M/F), Black, 6-in. (15.24 cm)

MODEL NUMBER: P137-06N-VGAB



Mini DP to VGA adapter connects a VGA monitor to the Mini DisplayPort or Thunderbolt 1/2 output on your laptop or computer.

### Features

**Mini DisplayPort to VGA Converter Connects Mini DP Source to VGA Display** This Keyspan® Mini DP to VGA active adapter connects a VGA monitor, projector or television to the Mini DisplayPort or Thunderbolt 1 or 2 port on your PC, Mac, Chromebook, MacBook, Microsoft Surface or other compatible computer or tablet. It features a male mDP connector and a female VGA connector, allowing you to continue using your existing VGA display and VGA cable to transmit video signals without the expense of a new mDP display.

**Transmits Outstanding 1080p Video for High-Definition Presentations** Ideal for classrooms, lecture halls and anywhere else you may need to connect to a VGA monitor, this Mini DisplayPort to VGA converter supports VGA computer video resolutions up to 1920 x 1200, including 1080p, and high-definition resolutions up to 1080p. The active adapter converts both Single-Mode and Dual-Mode (DP++) DisplayPort output. It's recommended for use with graphics cards, such as AMD Eyefinity, that do not output DP++ signals.

**Ready to Use Right from the Package, So You Can Plug and Play Immediately** The plug-and-play Mini DP to VGA adapter requires no software, drivers or external power, works with both Windows and Mac operating systems, and is compatible with laptops, tablets and other devices equipped with a female Mini DisplayPort or Thunderbolt 1 or 2 port. With its small size and built-in cable, the P137-06N-VGAB is recommended for stowing in your laptop bag and carrying to school or the office.

**3-Year Warranty** The P137-06N-VGAB is backed by a 3-year warranty, ensuring reliability and performance.

### Highlights

- Continue using your current VGA display without the expense of a new Mini DP monitor
- Delivers high-definition picture quality at resolutions up to 1920 x 1200, including 1080p
- Active adapter converts single- and dual-mode DP++ output for viewing on VGA display
- Compact unit fits easily into briefcase or laptop bag for instant use anywhere
- Plug-and-play operation with no software required for easy, immediate installation

### Applications

- Connect your laptop to a VGA monitor in a lecture hall or conference room for a video presentation
- Add a secondary monitor to the PC or laptop in your office or home workspace

### System Requirements

- Source device with Mini DisplayPort or Thunderbolt output
- Display device with VGA input
- Not for use with MST hubs

### Package Includes

- P137-06N-VGAB Keyspan Mini DisplayPort to VGA Active Adapter, Black



## Specifications

| OVERVIEW                            |                               |
|-------------------------------------|-------------------------------|
| UPC Code                            | 037332210579                  |
| Technology                          | VGA/SVGA; DisplayPort         |
| PHYSICAL                            |                               |
| Color                               | Black                         |
| Cable Length (ft.)                  | 1                             |
| Cable Length (m)                    | 0                             |
| Cable Length (in.)                  | 6                             |
| Cable Length (cm)                   | 15                            |
| ENVIRONMENTAL                       |                               |
| Operating Temperature Range         | 32 TO 158 F (0 TO 70 C)       |
| Storage Temperature Range           | 14 TO 176 F (-10 TO 80 C)     |
| Operating Humidity Range            | 10% TO 85% RH, NON-CONDENSING |
| Storage Humidity Range              | 5% TO 90% RH, NON-CONDENSING  |
| CONNECTIONS                         |                               |
| Side A - Connector 1                | MINI DISPLAYPORT (MALE)       |
| Side B - Connector 1                | HD15 (FEMALE)                 |
| STANDARDS & COMPLIANCE              |                               |
| Certifications                      | Tested to CE, FCC, RoHS       |
| WARRANTY                            |                               |
| Product Warranty Period (Worldwide) | 3-year limited warranty       |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>