

1U Single-Port KVM Console for Server Rack - 19 in.

Product ID: RKCONS1901



This rack-mount KVM console provides complete keyboard, monitor and mouse control for a single server or multiple servers, connected through a separate KVM switch (sold separately). The 19 in. console installs into 1U of rack space, offering a space-efficient solution for complete console control.

Maximize your IT budget, minimize your hassle

This KVM console provides all the essential controls you'll need to manage your server room at a low cost. The console features a built-in keyboard and a touchpad for intuitive control, as well as an LCD display that supports resolutions up to 1280x1024.

Maximize your screen space

This versatile LCD console has a 19 in. screen. The increased screen space allows you to run multiple applications on the same screen, increasing your productivity.

Clutter-free monitoring

The rack-mount LCD console slides out from 1U of rack space, enabling you to easily monitor and control a single server or multiple servers when connected through a KVM switch. The rack-mount VGA console features a handle that makes it easy to slide the console in and out of the server rack, keeping your area organized and clutter-free.

Hassle-free system integration

The rack console features a single-port KVM module, which enables you to connect it directly to a server. The module offers the flexibility you need to easily integrate it into your existing server infrastructure.

The RKCONS1901 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Control a single system, or dozens of KVM-connected computers
- Improve the internal space efficiency of your server cabinet
- Manage cabinet-mounted servers and KVM switches

Features

- Save money and reduce hassle with a cost-effective rack-mount LCD console
- Reduce your server room clutter with a 1U rack-mount design
- Large 19 in. screen allows you to run multiple applications at one time
- Intuitive system integration with direct support for a single server or KVM switch
- Built-in touchpad and keyboard
- Resolutions up to 1280x1024

Hardware	Warranty	2 Years
	Audio	No
	Cables Included	Yes
	Daisy-Chain	Yes
	Display Size	19in
	Front Door Key Lock	No
	KVM Ports	1
	Number of Monitors Supported	1
	Panel Type	Active Matrix TFT LCD
	PC Interface	USB
	PC Video Type	VGA
	Rack-Mountable	Yes
	U Height	1U
Performance	Brightness	250 cd/m ²
	Color Depth	8-bit, 16.7M colors
	Contrast Ratio	1000:1
	IP Control	No
	Maximum Analog Resolutions	1280 x 1024
	Maximum Number of Users	1
	MTBF	50,000 Hrs
	Pixel Pitch Support	0.264 x 0.264 mm
Supported Resolutions	1024x768	
	1280x720 (High-definition 720p)	
	1280 x 1024	
	<i>Lower resolutions are also supported</i>	
Connector(s)	Console Interface(s)	1 - VGA (15 pin, High Density D-Sub) Female Input
Indicators	LED Indicators	1 - power / status LED
Power	Power Consumption (In Watts)	17W
Environmental	Humidity	10 ~ 80% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Physical Characteristics	Maximum Mounting Depth	30.7 in [78 cm]

	Minimum Mounting Depth	19.7 in [50 cm]
	Product Height	1.7 in [4.3 cm]
	Product Length	21 in [53.3 cm]
	Product Width	19 in [48.3 cm]
	Weight of Product	27 lb [12.2 kg]
Packaging Information	Package Height	7.5 in [19 cm]
	Package Length	30.1 in [76.5 cm]
	Package Width	24.2 in [61.5 cm]
	Shipping (Package) Weight	35.4 lb [16 kg]
What's in the Box	Included in Package	1 - KVM console
		1 - KVM cable
		8 - M5 cage nuts
		8 - M5 screws
		5 - regional power cords (NA, JP, UK, EU, ANZ)
		2 - mounting rails (variable length)
		1 - quick-start guide

Product appearance and specifications are subject to change without notice.