

16-Port Rackmount KVM Console with 17" Display

Product ID: RKCONS1716K



Providing centralized control of up to 16 servers, this 16-port rackmount KVM console gives you easy access to your systems. With a minimal footprint, it mounts in a server rack or cabinet using only 1U of rack space.

An All-Inclusive Solution

The 1U rackmount console features a built-in keyboard, and a touchpad for intuitive control, as well as a 17-inch LCD display that supports resolutions up to 1280x1024.

This 16-port KVM console comes with everything you need to set up right out of the box:

- 16 VGA KVM Cables
- Mounting Rails
- M5 Cage Nuts and Screws

Simple System Integration

With direct access to 16 systems or servers, the 16-port KVM module gives you the flexibility you need to easily integrate the console into your existing server infrastructure.

StarTech.com Rack Consoles

Rack consoles provide convenient, rack-mounted control options for single servers or the entire server room. KVM consoles include LCD display, keyboard, and trackpad, all sliding into 1U of rack space. The RKCONS1716K is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Control up to 16 systems directly from the console, or dozens of KVM-connected computers
- Manage cabinet-mounted servers and KVM switches

Features

- Maximize your server rack space with a 1U rackmount design
- Intuitive system integration with direct support for up to 16 servers
- Ready to use with built-in touchpad and keyboard
- Save money and rack space with a cost-effective 1U rackmount LCD console
- Set up easily with all necessary mounting brackets, cables and screws included

| | | |
|----------------------------|------------------------------|--|
| Hardware | Warranty | 2 Years |
| | Audio | No |
| | Cables Included | Yes |
| | Daisy-Chain | No |
| | Display Size | 17in |
| | Front Door Key Lock | No |
| | KVM Ports | 16 |
| | Number of Monitors Supported | 1 |
| | Panel Type | Active Matrix TFT LCD |
| | PC Interface | USB |
| | PC Video Type | VGA |
| | Rack-Mountable | Yes |
| | U Height | 1U |
| | Performance | Aspect Ratio |
| Brightness | | 250 cd/m ² |
| Color Depth | | 8-bit, 16.7M colors |
| Contrast Ratio | | 1000:1 |
| Hot-Key Selection | | Yes |
| IP Control | | No |
| Maximum Analog Resolutions | | 1280 x 1024 |
| Maximum Number of Users | | 1 |
| MTBF | | 50, 000 Hrs |
| On-Screen Display | | Yes |
| Pixel Pitch Support | | 0.264 x 0.264 mm |
| Port Selection Support | | Push Button, Hotkeys, and OSD (On Screen Display) |
| Response Time | | 5ms |
| Supported Resolutions | | Resolutions up to 1280 x 1024 @ 60Hz |
| Viewing Angle | | 170° (H), 160° (V) |
| Connector(s) | Console Interface(s) | 1 - VGA (15 pin, High Density D-Sub) Female Output 2 - USB Type-A (4 pin) USB 2.0 Female Input 2 - PS/2 (6 pin, Mini-DIN) Female Input |
| | Host Connectors | 16 - VGA (15 pin, High Density D-Sub) Female Input |

| | | |
|---------------------------------|------------------------------|--|
| | Other Interface(s) | 1 - 15 Pin High Density D-Sub Female Input |
| Indicators | LED Indicators | 16 - Green/Red - Online/Selected LED |
| Power | Input Current | 1.5A |
| | Input Voltage | 100 ~ 240 AC |
| | Power Consumption (In Watts) | 23W |
| | Power Source | International Power Cords |
| Environmental | Humidity | 10 ~ 80% RH |
| | Operating Temperature | 0°C to 40°C (32°F to 104°F) |
| | Storage Temperature | -20°C to 60°C (-4°F to 140°F) |
| Physical Characteristics | Cable Length | 6 ft |
| | Color | Black |
| | Enclosure Type | Steel |
| | Maximum Mounting Depth | 35.4 in [90 cm] |
| | Minimum Mounting Depth | 22 in [56 cm] |
| | Product Height | 1.7 in [42.5 mm] |
| | Product Length | 22.9 in [581 mm] |
| | Product Weight | 30.3 lb [13.7 kg] |
| | Product Width | 17.6 in [448 mm] |
| Packaging Information | Shipping (Package) Weight | 46.4 lb [21 kg] |
| What's in the Box | Included in Package | 1 - KVM Console |
| | | 16 - KVM Cables |
| | | 8 - M5 Cage Nuts |
| | | 8 - M5 Screws |
| | | 5 - Regional Power Cords (NA, JP, UK, EU, ANZ) |
| | | 2 - Mounting Rails |
| | | 1 - Quick-Start Guide |

Product appearance and specifications are subject to change without notice.