

Rackmount KVM Console HD 1080p - Single Port VGA KVM with 17" LCD Monitor for Server Rack - Fully Featured 1U LCD KVM Drawer w/Cables & Hardware - USB Support - 50,000 MTBF

Product ID: RKCONS17HD



Providing centralized control of your single PC or dozens of servers, this HD rackmount KVM console also gives you easy access to and visibility of your system while it's mounted in a server rack or cabinet. Connected to your servers through a separate KVM switch (sold separately), the LCD console installs into 1U of rack-space, offering a space-efficient solution for complete console control.

High-Definition LCD Monitor

The 1080p KVM console's monitor is 17.3" and LED back-lit, for low power consumption. It supports high-definition resolutions up to 1920x1080 providing sharper video performance. This HD console also provides more screen space, helping you to run multiple applications on the same screen, increasing your productivity.

Clutter-Free Monitoring

The rack-mount LCD console slides out from 1U of rack space, enabling you to easily monitor and control a single server or multiple servers when connected through a KVM switch. The rackmount VGA KVM features a handle that makes it easy to slide the console in and out of the server rack, keeping your area organized and clutter-free.

Simple Setup

This single-port KVM console comes with everything you need to set up:

- 1 Audio Cable
- 1 Set of KVM Cables (VGA)
- 2 Rear Mounting Brackets
- M5 Cage Nuts and Screws

Cost Effective Solution

This KVM console provides all the essential controls you'll need to manage your server room at a low cost. The console features a built-in keyboard and a touchpad for intuitive control, as well as a high-definition LCD display.

StarTech.com offers a wide selection of KVM consoles to help you access your systems more efficiently without the expense and clutter of extra peripherals. This rackmount KVM console is backed by a 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Large server farms
- Colocation facilities

Features

- High Definition: Rackmount KVM console w/high-resolution widescreen (16:9) 1080p LCD panel is perfect for applications needing extra detail or substantial info on one screen E.g. IP camera monitoring
- Wide compatibility: This HD KVM console drawer works with virtually any KVM switch brand or model that supports VGA and USB interfaces and conveniently slides into the server rack when not in use
- Versatile Interfaces: Rack mount monitor with 17.3" Active Matrix TFT 16:9 widescreen | 1U height | Single Port | Full keyboard + Trackpad | Integrated Power Supply | Supports VGA + USB
- Max Durability: Features durable steel housing and rails that withstand frequent use, rated to work in environments from 0 to 40 deg. C and a 44,230 hour MTBF with 24/5 Tech Support
- Tested and Proven: Our KVM consoles are backed by a 2 year warranty with 24/5 by multi-lingual tech support based in North America with free technical support for the life of the product.

Hardware	Warranty	2 Years
	Audio	No
	Cables Included	Yes
	Daisy-Chain	No
	Display Size	17.3"
	KVM Ports	1
	Number of Monitors Supported	1
	Panel Type	Active Matrix TFT LCD
	PC Interface	USB
	PC Video Type	VGA
	Rack-Mountable	Yes
	U Height	1U
Performance	Aspect Ratio	16:9
	Brightness	300 cd/m ²
	Color Depth	6-bit, 262144 colors
	Contrast Ratio	800:1
	IP Control	No
	Maximum Analog Resolutions	1920x1080
	Maximum Number of Users	1
	MTBF	50000 Hours
	Pixel Pitch Support	0.1989 x 0.1989 mm
	Supported Resolutions	Resolutions up to 1920x1080 @ 60Hz
Connector(s)	Host Connectors	1 - HD15 (15 pin, High Density D-Sub) Female Input
	Other Interface(s)	1 - IEC 60320 C14 Power Female Input
Special Notes / Requirements	Note	The minimum mounting depth of this rackmount console is less than the length of the console itself. Please consider the length of the rackmount console when evaluating if it will fit into your rack.
Indicators	LED Indicators	1 - Power / Status LED
Power	Input Current	1.5A
	Input Voltage	100 - 240 AC
	Power Consumption (In Watts)	13W

	Power Source	International Power Cords
Environmental	Humidity	10 ~ 80% RH
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Physical Characteristics	Cable Length	1.8 m
	Color	Black
	Material	Steel
	Maximum Mounting Depth	33.5 in [85 cm]
	Minimum Mounting Depth	20.1 in [510 mm]
	Product Height	1.7 in [4.3 cm]
	Product Length	22.2 in [56.5 cm]
	Product Width	19 in [48.3 cm]
Weight of Product	30.3 lb [13.7 kg]	
Packaging Information	Package Height	7.3 in [18.5 cm]
	Package Length	30.1 in [76.5 cm]
	Package Width	24.2 in [61.5 cm]
	Shipping (Package) Weight	35.4 lb [16 kg]
What's in the Box	Included in Package	1 - KVM console
		1 - KVM cable
		8 - M5 cage nuts
		8 - M5 screws
		5 - regional power cords (NA, JP, UK, EU, ANZ)
		1 - quick-start guide
		2 - mounting rails

Product appearance and specifications are subject to change without notice.