



**AOC Monitors  
USB Powered  
Portable Monitor**

**USB Series**  
15.6", 1920 x 1080 Full HD

**I1601FWUX**

## 16" Class, USB Type-C, Full HD, IPS Monitor. Sleek Design.

The I1601FWUX USB powered portable LED backlit monitor is a must-have laptop or desktop accessory. The widescreen monitor receives both power and video signal via a single USB Type-C cable for plug-and-play connection; it does not require a power cord or VGA cable, and comes with a foldable flexi-stand for maximum flexibility.

### Key Features:

- 15.6" 1920x1080 Full HD Resolution
- IPS Display for wide viewing angles and truer colors
- USB Type-C Technology for USB-powered plug-and-play connection
- 5ms response time for smooth visuals
- Ultra-slim and lightweight with stylish piano-black glossy design
- Auto-pivot feature for viewing in landscape or portrait mode according to display's orientation
- Perfect accessory for the frequent traveler or on-the-go presentation
- Foldable flexi-stand for landscape and portrait mode
- LowBlue Mode technology to reduce harmful light

### USB Type-C Monitor

The updated portable USB Type-C is sleeker in design and utilizes the newest USB Type-C port for connecting to your PC or Laptop. USB Type-C allows both power and data streams simultaneously. It's the only cable needed between your source and the AOC I1601FWUX portable monitor, creating an ultra-clean setup



Designed with a piano-black glossy finish, this USB monitor has a 15.6" diagonally viewable image. The I1601FWUX offers a 700:1 contrast ratio, 11ms response time, and a beautiful 1920x1080 Full HD resolution at 60Hz.



### Flexi-stand Smart Cover

The I1601FWUX USB Monitor has a foldable flexi-stand for viewing in landscape or portrait mode. Landscape mode is ideal for presentations and Excel sheets, while the Portrait mode conveniently gives you an easy vertical view of your instant messaging program, or sidebars such as search results. This monitor has the unique auto-pivot feature that automatically adjusts the image according to the display's orientation, so you will never have to change settings as you switch between landscape and portrait mode.

### Ultra Lightweight and Slim Portability at Its Best

It's ultra-lightweight and slim for great portability, making it perfect for business presentations, the frequent traveler, photo frame applications, and dual monitor setups on-the-go. The I1601FWUX USB Monitor is the solution for the frequent traveler who needs to pack multiple displays, as it easily fits into a backpack or the carry case that comes with the USB monitor.



### LowBlue Mode

LowBlueLight via software solution. Decrease harmful blue light by controlling color temperature while keeping the vivid color.



### Wide Viewing Angles

IPS panels have the best color uniformity at any viewing angle, such as a perfect supermodel without flaws.



## I1601FWUX Specification

<b>Cabinet Color</b>	Piano-Black Glossy
<b>Panel</b>	FT Active Matrix LCD, LED Backlight, IPS Panel 15.6" Class Widescreen, 16:9 Aspect Ratio 15.6" Viewable Image Size, Diagonal
<b>Pixel Pitch</b>	0.179(H)mm x 0.179(V)mm
<b>Display Area</b>	344.16 mm x 193.59 mm
<b>Brightness</b>	220 cd/m <sup>2</sup> (typ)
<b>Contrast Ratio</b>	700:1 (static)
<b>Response Time</b>	5ms (gtg)
<b>Viewing Angle</b>	Horizontal: 160 Degrees (CR>10) Vertical: 160 Degrees (CR>10)
<b>Scanning Frequency</b>	30 -83KHz (H) 50 -76 Hz (V)
<b>Optimal Resolution Recommended</b>	1920x1080@60Hz 1920x1080@60Hz
<b>Supported Resolutions</b>	(All in extended mode) 640x480@60Hz, 800x600@60Hz, 1024x768@60Hz, 1366x768@60Hz, 1920x1080@60Hz
<b>Color Depth</b>	262K colors
<b>Input Signal</b>	1 x USB Type-C (DP Alt mode)
<b>User Control</b>	NA
<b>Adjustability</b>	Tilt: 5°~25°
<b>Power Source</b>	PC USB 5V
<b>Power Consumption</b>	8W (typical), Standby: .5W
<b>Regulations</b>	cTUVus, FCC, RoHS, EPA, Windows 8/10 compatible
<b>Other Features</b>	Ultra Slim, Foldable Stand, Low Power Consumption, Low Blue light, Smart UI to adjust USB monitor via PC software, Better Picture
<b>Dimensions (WxHxD mm)</b>	Monitor: 376.2x235.2x8.5 Carton: 84x295x442
<b>Dimensions (WxHxD inches)</b>	14.81x9.26x0.33 Carton: 3.3x 11.6x17.4
<b>Weight (Net)</b>	1.81 lbs ( 0.824 kgs) Net
<b>Weight (Gross)</b>	3.469 lbs ( 1.574 kgs) Gross
<b>Loading Qty w/pallet</b>	20'=2352pcs; 40' Std=4704pcs.
<b>UPC Code</b>	685417714582
<b>What's in the Box</b>	15.6" Monitor, USB-Type C cable, smart cover case, QSG
<b>Compatibility</b>	The host laptop must have a USB Type-C connection that supports DisplayPort Alternate Mode for the monitor to function properly.

1. Wall mount arm & bracket not included. Actual product may vary from image shown on datasheet. The information contained herein is subject to change without notice. AOC shall not be liable for technical or editorial errors or omissions contained herein. All other trademarks are property of their respective owners. For more information, visit [us.aoc.com](http://us.aoc.com) or call 888-838-6388