



Vertical Rackmount 24-Output C13 Power Distribution Unit (PDU)

With Power Switch, Removable Power Cable and Rear C14 Input

Part No.: **163644**

Our new 19" rackmountable PDU range puts Intellinet innovation and practicality on display. This comprehensive line offers a wide selection of tools to protect your valuable I.T. equipment. An integrated, removable cable plugs conveniently into the rear C14 input of the unit.

Features:

- Vertical rackmountable Power Distribution Unit
- Socket outlet standard IEC320 C13
- Socket input standard IEC320 C14
- Control & protection functions: Power switch
- Cable specification: standard 2 m (6.6 ft.) removable power cord
- Three-Year Warranty

Specifications:

General

- Vertical Rackmount
- Socket/outlet standard: IEC320 C13
- Outlets: 24
- Cable specification: standard 2 m (6.6 ft.) removable power cord
- Size: 1142 (L) x 45 (W) x 45 (H) [mm] 44.96 (L) x 1.77 (W) x 1.77 (H) [in]
- Electrical rating: 110 - 250V AC
- Maximum load current: 16 A (IEC EU 10 A, North America 15 A)

Package Contents

- Vertical Rackmount 24-Output C13 Power Distribution Unit (PDU)
- 2m (6.6 ft.) power cord
- Two M6*12 screws
- Two M6 nuts
- Two plastic washers

