



Vertical Rackmount 24-Output Power Distribution Unit (PDU)

20 x C13 & 4 x Output C19, Removable Power Cable, Rear C14 Input

Part No.: **163675**

Our new, 19" rackmountable PDU range displays Intellinet innovation and practicality. This comprehensive line offers a wide selection of tools to protect your valuable I.T. equipment. An integrated, removable cable plugs conveniently into the rear C14 input of the unit.

Features:

- Vertical rackmountable Power Distribution Unit
- Socket outlet Standard IEC320 C13 (x 20) & IEC320 C19 (x 4)
- Socket input Standard IEC320 C14
- Cable specification: standard 2 m (6.6 ft.) removable power cord
- Three-Year Warranty


Specifications:

General

- Vertical Rackmount
- Socket/outlet standard: IEC320 C13 (x 20) & IEC320 C19 (x 4)
- Outlets: 24
- Cable specification: standard 2 m (6.6 ft.) removable power cord
- Size: 1133.6 (L) x 45 (W) x 45 (H) [mm] / 44.63 (L) x 1.77 (W) x 1.77 (H) [in]
- Electrical rating: 110 - 250V AC
- Maximum load current: 16 A (IEC EU 10 A, North America 15 A)

Package Contents

- Vertical Rackmount 24-Output Power Distribution Unit (PDU)
- 2 m (6.6 ft.) power cord
- Two M6*12 screws
- Two M6 nuts
- Two plastic washers



For more information on Intellinet products, consult your local dealer or visit www.intellinet-network.com.

All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.