

Power Cord Splitter, C14 to 4xC13 PDU Style - 10A, 250V, 18 AWG, 18-in. (45.72 cm), Black

MODEL NUMBER: P004-18N-4XC13



C14-to-C13 splitter allows 4 devices with C14 inlets to share one AC power input cord and one C13 outlet on a PDU or UPS system.

Features

C14-to-C13 X-Style Splitter Cord Connects 4 Devices with C14 Inlets to One C13 Outlet This IEC-320-C14 to IEC-320-C13 splitter allows four devices with C14 power inlets to share one AC input cord and one C13 outlet. This C14 male to C13 female cord features a C14 end for connecting to an AC power source on a PDU, surge protector or UPS system and four C13 ends for connecting to devices. By connecting four devices to one outlet, the power cord splitter frees up space in a PDU or surge protector and helps reduce cable clutter.

IEC Cable Powers a Wide Variety of Essential Electronics With this PC power splitter, a single C13 outlet can power four devices, such as computers, monitors, printers, instrument amplifiers and other equipment compatible with a C13 connector. Ideal for areas where AC outlets are limited, such as rack cabinets, this IEC cable is compatible with Tripp Lite power and extension cords.

Highlights

- Connects 4 devices to one AC outlet to save space and reduce cable clutter
- Recommended for powering multiple computers, monitors or other compatible peripherals
- C14 end connects to PDU or UPS power; C13 ends connect to devices' C14 inlets
- C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable

Applications

- Connect 4 devices like computers, monitors, scanners and printers to one power outlet in your home office, work space or dorm room
- Cut cable clutter by powering up to 4 monitors in a multi-monitor display mount with a single cord
- Save space in a 0U vertical rack-mount PDU by plugging 4 rack devices into one outlet

Package Includes

- P004-18N-4XC13 C14 Male to C13 Female Splitter, PDU Style, 18 in., Black

Specifications

OVERVIEW	
UPC Code	037332205261
Device Compatibility	Computer; Monitor/HDTV; Printer; Scanner; UPS; PDU



Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	100-250
PHYSICAL	
Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	SJTW
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
Cable Length (ft.)	1.5
Cable Length (m)	0.46
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	1.52 x 21.59 x 31.75
Shipping Dimensions (hwd / in.)	0.60 x 8.50 x 12.50
Shipping Weight (kg)	0.24
Shipping Weight (lbs.)	0.54
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	(4) IEC-320-C13
SPECIAL FEATURES	
High Voltage	Yes
Locking Plug	No
STANDARDS & COMPLIANCE	
Certifications	UL LISTED
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

<https://www.tripplite.com/products/product-certification-agencies>