

SAMSUNG

Worry-free printing, delivered more affordably

The reliable, cost conscious office printer you've been waiting for

Ctrl

P



Samsung Monochrome Laser Printer
ML-3750ND



Cost conscious

With economy front of mind, meet one of the most cost conscious printers around.



Extra high yield toner can print even the biggest jobs easily and economically. These special cartridges can print 15,000 pages, provide a lower cost per page and require fewer replacements.



Just press the **ECO button** and you switch to **Toner Save Mode**. You can also convert printouts to two or four pages per sheet and enable duplex printing. In the long term, too, it proves an excellent investment. The ML-3750ND will save you more money in **Total Cost of Ownership** than its competitors.



And it doesn't stop there. The unique **Result Simulator** lets you see how much CO₂, electricity and paper you've saved.



The Samsung ML-3750ND

Why shouldn't office printing be simple, profitable and productive? From easy-to-use design and extra high yield toner, to the very latest and cost-effective ownership, you'll discover the ML-3750ND fits in

Worry-free printing

You'll find the ML-3750ND so easy to use, thanks to a control panel with a numeric keypad that lets you check the status of your job.



What's more, an Anti-Jam friction roller minimises the risk of mis-feeds or multiple paper feeds.



And if you want personal jobs to remain personal, then you can keep your documents from being printed until the unique PIN has been entered.

Our range of useful software applications are on-hand for easier and more efficient printing.

- **Easy Printer Manager** lets you manage all your printers from one location.
- **Universal Print Driver** makes it quick and easy to search for compatible devices, check their status, then send jobs to available printers.
- **Samsung AnyWeb Print** lets you collect and print information from the web – saving time and energy.
- **Samsung SyncThru Web Service** uses a familiar web interface, so you can check status information, customise settings and receive email alerts remotely.
- For proactive monitoring and remote management through an easy-to-use dashboard, **SyncThru Admin 5** delivers. It lets you configure and update devices, track supplies and compile reports.
- Finally, **CounThru** enables you to remotely monitor printer activity, calculate and manage the costs of your entire printer fleet – giving you extra freedom.



fast anti-jam technology
to your office life perfectly.

High productivity

No matter what size the print job, the ML-3750ND can tackle it thanks to its lightning-fast performance.



Impressive processing speed, high CPU and adequate memory – it all adds up to faster output. In fact, it can power through a 50-page Powerpoint presentation 20% quicker than its competitors*.



Not only that, the ML-3750ND can handle a wide range of paperweights, from speciality paper to card. Plus, with an **820 sheet** total paper capacity, it's always stacked and ready to go.



And good news if you have a lot of print jobs arriving from a lot of different people; **1 Gigabit LAN** support enables many documents from multiple users to be transmitted and processed quickly.

* Figure based on internal test report

Configuration


Samsung Monochrome Laser Printer ML-3750ND



Control Panel
Output Tray
Multi-Purpose Tray
Tray
Paper Level Indicator



Display
Menu Button
OK Button
Back Button
Numeric Keypad
Cancel Button
Eco Button
Power Button
Status LED



Network Port
Rear Cover
USB Port 1
USB Port 2 (ML-3753ND only)
IEEE 1284 Parallel Connector
Power Supply Jack
Power Receptacle
Power-switch

Supplies & Option




Black Toner Cartridge
MLT-D305L



Black Toner Cartridge
MLT-D305S



Second Cassette Feeder
ML-S3710A



512MB Memory
ML-MEM307



Parallel Connector
ML-PAR100

Specifications

ML-3750ND

Print

Speed (Mono)	Up to 35 ppm in A4 (37 ppm in Letter)
First Print Out Time (Mono)	As fast as 6.5 sec
Resolution	Optical : 600 x 600 Enhanced : Up to 1200 x 1200 dpi effective output
Emulation	PostScript3, PCL6/5e, IBM ProPrinter, EPSON
Duplex	Built-in

Paper Handling

Input Capacity and Types	250-sheet Cassette 50-sheet Multi Purpose Tray
Output Capacity and Type	150-sheet Face-Down 1-sheet Face-up
Media Size	76 x 127 mm (3" x 5") - 216 x 356 mm (8.5" x 14") Envelope : Monarch / No.10 / DL / C5 / C6
Media Type	Plain, Thin, Thick, Thicker, Cotton, Colored, Envelope, Transparency, Pre-Printed, Recycled, Labels, Bond, Card stock, Archive
Envelope Capacity	5-sheet from Multi Purpose Tray

General Feature

Processor	Samsung 533 MHz
Interface	Ethernet 10/100/1000 Base TX High Speed USB 2.0
Noise Level	Less than 52dBA (Printing) Background Noise Only (Less than 26 dBA) (Standby)
Memory/Storage	128 MB (Max. 512MB)
OS Compatibility	Windows 8 / 7 / Vista / XP / 2000 / 2008R2 / 2008 / 2003, Mac OS X 10.4 - 10.8, Various Linux / Unix
Duty Cycle, Monthly	80,000 sheets
Dimension (WxDxH)	366 x 368 x 272.9 mm (14.4 x 14.4 x 10.7 inch)
Weight	10.09kg (Inc. Toner) 8.81kg (exc. Toner)
Power Consumption	1.4 W (Sleep) 60 W (Ready) 550 W (Active AVG.)

Consumables

Black Toner Cartridge	High Yield: Average cartridge Yield 15K standard pages. (Ships with 7,000 pages Starter Toner Cartridge) Declared cartridge yield in accordance with ISO/IEC 19752.
-----------------------	---

Options

Options	520-sheet Cassette Tray @80g/m ² (550-sheet Cassette Tray @75g/m ²) / 512MB Memory / IEEE 1284B Parallel Connector
---------	--

* Specifications may vary depending on the model

Copyright © 2012 Samsung Electronics Co. Ltd. All rights reserved. Samsung is a registered mark of Samsung Electronics Co. Ltd. Specification and design are subject to change without notice. Non-metric weights and measurements are approximate. All data were deemed correct at time of creation. Samsung is not liable for errors or omissions. All brand, product, service names, and logos are trademarks and/or registered trademarks of their respective owners, and are hereby recognized and acknowledged.

Contact :
Web: www.samsung.com

