



Westinghouse

SPECIFICATION SHEET

Item Number 7255900

Panorama Ceiling Fan

52" Chrome Finish Reversible Blades (High Gloss White/Black) Includes Light Kit with Opal Frosted Glass Shades

Specifications

Size	52"
Blades.....	Reversible MDF Blades (High Gloss White/High Gloss Black)
Blade Pitch.....	12°
Approved Location	Indoor
Suggested Room Size	Large Room (up to 15x15)
Down Rod.....	3/4" x 4"
Installation.....	Combo
Max. Ceiling Angle.....	15°
Lead Wire	54"
Light Bulb Usage.....	Includes (4) Medium (E26) Base, 14 Watt CFL Mini-Twists
Control.....	Remote Control Adaptable
Motor Finish.....	Chrome
Motor Material	Silicon Steel Motor 153mm x 17mm
Reverse Airflow.....	Yes
Capacitor	Triple
Switch Housing Cap.....	Not Included



Reversible High Gloss Black Finish Blades

Energy Information


Airflow Efficiency.....	75 Cubic Feet Per Minute Per Watt
Electricity Use.....	63 Watts (excludes lights)
Airflow.....	4733 Cubic Feet per Minute
Max rpm	160

Warranty

Ceiling fans backed by our Limited Lifetime Warranty have a lifetime motor warranty and a 2-year warranty on all other parts.



A. Top of Canopy to Bottom of Blades	12.6"
B. Top of Canopy to Bottom of Switch House	9"
C. Top of Canopy to Bottom of Canopy	2.5"
D. Width of Motor Housing.....	10.8"
E. Width of Canopy.....	5.1"
F. Top of Canopy to Bottom of Glass	15.9"



Compact Fluorescent Lamps contain mercury. For more on clean up and safe disposal, visit epa.gov/cfl.

Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are registered trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.