



# Westinghouse

## SPECIFICATION SHEET

Item Number 7247700

### Castle Ceiling Fan

52" Brushed Nickel Finish Reversible Blades  
(Weathered Maple/Beech) Includes Light Kit with Opal  
Frosted Glass

#### Specifications

Size .....	52"
Blades.....	Reversible Plywood Blades (Weathered Maple/Beech)
Blade Pitch.....	12°
Approved Location .....	Indoor
Suggested Room Size .....	Large Room (up to 15x15)
Down Rod.....	3/4" x 6"
Installation.....	Combo
Max. Ceiling Angle.....	18°
Lead Wire .....	78"
Light Bulb Usage.....	Includes (2) Medium (E26) Base, 13 Watt CFL Mini-Twists
Control.....	Remote Control Adaptable
Motor Finish.....	Brushed Nickel
Motor Material .....	Cold Rolled Steel Motor 153mm x 15mm
Reverse Airflow.....	Yes
Capacitor .....	Triple
Switch Housing Cap.....	Not Included



Reversible Beech  
Finish Blades

#### Energy Information


Airflow Efficiency.....	70 Cubic Feet Per Minute Per Watt
Electricity Use.....	56 Watts (excludes lights)
Airflow.....	3914 Cubic Feet per Minute
Max rpm .....	171

#### Warranty

Ceiling fans backed by our Limited Lifetime Warranty have a lifetime motor warranty and a 2-year warranty on all other parts.



A. Top of Canopy to Bottom of Blades .....	11.4"
B. Top of Canopy to Bottom of Switch House .....	12.6"
C. Top of Canopy to Bottom of Canopy .....	2.4"
D. Width of Motor Housing.....	10.5"
E. Width of Canopy.....	5.1"
F. Top of Canopy to Bottom of Glass .....	16"



Compact Fluorescent Lamps contain mercury. For more on clean up and safe disposal, visit [epa.gov/cfl](http://epa.gov/cfl).

Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.

Call 1-800-999-2226 or visit [www.westinghouselighting.com](http://www.westinghouselighting.com).

WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are registered trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.