

Item Number 7247300

Alloy Ceiling Fan

42" Brushed Nickel Finish Reversible Blades
(Beech/Wengue) Includes Light Kit with Opal Frosted Glass

Specifications

Size	42"
Blades	Reversible MDF Blades (Beech/Wengue)
Blade Pitch	13°
Approved Location	Indoor
Suggested Room Size	Small Room (10x10) or smaller
Down Rod	3/4" x 4"
Installation	Down Rod Only
Max. Ceiling Angle	18°
Lead Wire	78"
Light Bulb Usage	Includes (2) Candelabra (E12) Base, 40 Watt G16 1/2 Lamps
Control	Remote Control Adaptable
Motor Finish	Brushed Nickel
Motor Material	Silicon Steel Motor 153mm x 10mm
Reverse Airflow	Yes
Capacitor	Dual
Switch Housing Cap	Not Included



Reversible Wengue
Finish Blades

Energy Information


Airflow Efficiency	80 Cubic Feet Per Minute Per Watt
Electricity Use	51 Watts (excludes lights)
Airflow	4083 Cubic Feet per Minute
Max rpm	215



Warranty

Ceiling fans backed by our Limited Lifetime Warranty have a lifetime motor warranty and a 2-year warranty on all other parts.

A. Top of Canopy to Bottom of Blades	6.4"
B. Top of Canopy to Bottom of Switch House	11"
C. Top of Canopy to Bottom of Canopy	2.5"
D. Width of Motor Housing	6.8"
E. Width of Canopy	5.1"
F. Top of Canopy to Bottom of Glass	11.8"



Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

®, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are registered trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.