

Item Number 7204300

Great Falls Ceiling Fan

52" Oil Rubbed Bronze Finish Dark Walnut ABS Blades
Includes Light Kit with Frosted Amber Glass

Specifications

Size	52"
Blades.....	ABS Blades (Dark Walnut)
Blade Pitch.....	12°
Approved Location	Indoor/Outdoor
Suggested Room Size.....	Large Room (up to 15x15)
Down Rod.....	3/4" x 4"
Installation.....	Combo
Max. Ceiling Angle.....	18°
Lead Wire	54"
Light Bulb Usage.....	Includes (1) Medium (E26) Base, 10 Watt Omni LED Lamp
Control	Remote Control Adaptable
Motor Finish.....	Oil Rubbed Bronze
Motor Material	Silicon Steel Motor 153mm x 15mm
Reverse Airflow.....	Yes
Capacitor	Triple
Switch Housing Cap.....	Not Included



Energy Information


Airflow Efficiency.....	74 Cubic Feet Per Minute Per Watt
Electricity Use.....	55 Watts (excludes lights)
Airflow.....	4070 Cubic Feet per Minute
Max rpm	67



Warranty

Ceiling fans backed by our Limited Lifetime Warranty have a lifetime motor warranty and a 2-year warranty on all other parts.

A. Top of Canopy to Bottom of Blades	10.8"
B. Top of Canopy to Bottom of Switch House	12.8"
C. Top of Canopy to Bottom of Canopy	2.7"
D. Width of Motor Housing.....	7.9"
E. Width of Canopy.....	5.2"
F. Top of Canopy to Bottom of Glass	20.1"



Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

®, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are registered trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.