



Westinghouse

SPECIFICATION SHEET

Item Number 7203200

Cassidy Ceiling Fan

36" Brushed Nickel Finish Reversible Blades
(Wengue/Silver) Includes Light Kit with Opal Frosted
Glass

Specifications

Size	36"
Blades.....	Reversible MDF Blades (Wengue/Silver)
Blade Pitch.....	12°
Approved Location	Indoor
Suggested Room Size	Small Room (10x10) or smaller
Down Rod.....	3/4" x 4"
Installation.....	Combo
Max. Ceiling Angle.....	18°
Lead Wire	24"
Light Bulb Usage.....	Includes (2) Candelabra (E12) Base G16 1/2 Lamps, 40 Watt
Control.....	Remote Control Adaptable
Motor Finish.....	Brushed Nickel
Motor Material	Silicon Steel Motor 153mm x 12mm
Reverse Airflow.....	Yes
Capacitor	Dual
Switch Housing Cap.....	Not Included



Reversible Silver
Finish Blades

Energy Information


Airflow Efficiency.....	55 Cubic Feet Per Minute Per Watt
Electricity Use.....	43 Watts (excludes lights)
Airflow.....	2352 Cubic Feet per Minute
Max rpm	288

Warranty

Ceiling fans backed by our Limited Lifetime Warranty have a lifetime motor warranty and a 2-year warranty on all other parts.



A. Top of Canopy to Bottom of Blades	11.2"
B. Top of Canopy to Bottom of Switch House	11.8"
C. Top of Canopy to Bottom of Canopy	2.1"
D. Width of Motor Housing.....	8.6"
E. Width of Canopy.....	5.1"
F. Top of Canopy to Bottom of Glass	16.5"



Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

©, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are registered trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.