



Westinghouse

SPECIFICATION SHEET

Item Number 7202100

Urban Gale Ceiling Fan

52" White Finish White ABS Blades

Specifications

Size	52"
Blades.....	ABS Blades (White)
Blade Pitch.....	9°
Approved Location	Indoor
Suggested Room Size	Large Room (up to 15x15)
Down Rod.....	1/2" x 12"
Installation.....	Down Rod Only
Max. Ceiling Angle.....	N/A
Lead Wire	54"
Light Bulb Usage.....	N/A
Control.....	Remote Control Included
Motor Finish.....	White
Motor Material	Cold Rolled Steel Motor 171mm x 12mm
Reverse Airflow.....	Yes
Capacitor	Dual
Switch Housing Cap.....	Not Included



Energy Information

Airflow Efficiency.....	87 Cubic Feet Per Minute Per Watt
Electricity Use.....	66 Watts (excludes lights)
Airflow.....	5734 Cubic Feet per Minute
Max rpm	110


Warranty

Ceiling fans backed by our Limited Lifetime Warranty have a lifetime motor warranty and a 2-year warranty on all other parts.

Caution

This ceiling fan has thin blades and operates at higher speeds than traditional ceiling fans. Severe injury can result if any part of the body comes in contact with these fast-moving blades. For safe operation, this product must be installed with a minimum clearance of 10 feet from the floor to the lowest edge of the fan blades.

A. Top of Canopy to Bottom of Blades	18.1"
B. Top of Canopy to Bottom of Switch House	15.8"
C. Top of Canopy to Bottom of Canopy	2.4"
D. Width of Motor Housing.....	18.9"
E. Width of Canopy.....	5.1"
F. Top of Canopy to Bottom of Glass	N/A



Specifications are subject to change without notice, please visit www.westinghouselighting.com for latest information.

Call 1-800-999-2226 or visit www.westinghouselighting.com.

©, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are registered trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.